

SITOR fuse link, with blade contacts, NH000, In: 50 A, gR, Un AC: 690 V, Un DC: 440 V, front indicator



Model	
Product brand name	SETRON
Product designation	SITOR fuse link
Design of the product	With blade contacts
Design of an identification indicator	front indicator
Design of the switching contact	With bolt-on links, silver-plated
Design of the fuse link	SITOR, LV HRC design
General technical data	
Size of fuse system / acc. to DIN EN 60269-1	NH000
Operating class of the fuse link	gR
Supply voltage	
Type of voltage	AC/DC
Current / at AC / rated value	50 A
Supply voltage	
• at AC / rated value	690 V
• at DC	440 V
Product details	
Product description	Not non-interchangeable

## Mechanical Design

Mounting position Any, preferably vertical

## Environmental conditions

Ambient temperature -20 ... +50 °C

Environmental category -20 to +50 at 95% relative humidity

## Certificates

Reference code

- acc. to DIN EN 61346-2 F
- acc. to DIN EN 81346-2 F

## Declaration of Conformity



EG-Konf.

## Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NE8817-0MK>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3NE8817-0MK>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NE8817-0MK](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NE8817-0MK)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



Type	Dimensions							
	A	B	D	H	J	K	M	L
<b>3NE88..-0MK</b>	53	21	51,5	15	43	6	35	78,5
<b>3NE82..-0MK</b>	62,5	44	70,5	20	53	6	40	135
<b>3NE83..-0MK</b>	68	50	70,5	25	61	6	48	150

