

SITOR fuse holder 22x 127 63 A 1500 V AC/1000 V DC 1-pole



Model	
Product designation	SITOR fuse switch disconnecter
Design of the operating mechanism	Cover handle
General technical data	
Number of poles	1
Size of fuse link	Other
Usage category	AC20B/DC20B
Size of the fuse link	22x127 mm
Operating voltage	
<ul style="list-style-type: none"> • at AC / rated value / maximum • at DC / rated value / maximum 	<p>1 500 V</p> <p>1 000 V</p>
Protection class	
Protection class IP / on the front	IP20
Current	
Continuous current / rated value	63 A
Suitability	
Suitability for use	

• Main switch	No
• switch disconnector	No
• EMERGENCY OFF switch	No
• safety switch	No

Product function

Product function / fuse monitoring	No
------------------------------------	----

Short circuit

Conditional short-circuit current (I _q) / rated value	50 kA
---	-------

Connections

Connectable conductor cross-section	
• solid	1 ... 50 mm ²
• stranded	1 ... 50 mm ²
Type of electrical connection / for main current circuit	screw-type terminals

Mechanical Design

Height	200 mm
Depth	102 mm
Mounting type	
• floor mounting	Yes
• front mounting	No
• rail mounting	No
Net weight	480 g

Certificates

Reference code	
• acc. to DIN EN 61346-2	F
• acc. to DIN EN 81346-2	F

General Product Approval

[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=3NC2391-0MK>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NC2391-0MK>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NC2391-0MK

CAX-Online-Generator

<http://www.siemens.com/cax>

