

SITOR fuse link, with internal thread and bolt terminal, In: 350 A, aR,  
Un AC: 800 V, Un DC: 440 V, front indicator



Model	
Product brand name	SETRON
Product designation	SITOR fuse link
Design of the product	With female thread and stud terminal
Design of an identification indicator	front indicator
Design of the fuse link	Fuses for special applications
General technical data	
Size of fuse system / acc. to DIN EN 60269-1	others
Operating class of the fuse link	aR
Varying load factor (WL)	0.9
Supply voltage	
Type of voltage	AC/DC
Current / at AC / rated value	350 A
Supply voltage	
• at AC / rated value	800 V
• at DC	440 V
Switching capacity	
Switching capacity current	

- acc. to IEC 60947-2 / rated value 100 kA

### Dissipation

Power loss [W]	80 W
Power loss [W]	80 W
<ul style="list-style-type: none"> <li>• for rated value of the current / at AC / in hot operating state / per pole</li> </ul>	80 W
<ul style="list-style-type: none"> <li>• maximum</li> </ul>	80 W

### Product details

Product description	Not non-interchangeable
---------------------	-------------------------

### Mechanical Design

Mounting position	Any, preferably vertical
-------------------	--------------------------

### Environmental conditions

Ambient temperature	-20 ... +50 °C
Environmental category	-20 to +50 at 95% relative humidity

### Certificates

Reference code	
<ul style="list-style-type: none"> <li>• acc. to DIN EN 61346-2</li> </ul>	F
<ul style="list-style-type: none"> <li>• acc. to DIN EN 81346-2</li> </ul>	F

### General Product Approval

### Declaration of Conformity

[Miscellaneous](#)



### Further information

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

#### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NC5531>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NC5531>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NC5531](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC5531)

#### CAX-Online-Generator

<http://www.siemens.com/cax>

#### Tender specifications

<http://www.siemens.com/specifications>

