

SITOR fuse link, with slotted blade contacts, NH2, In: 500 A, gR, Un AC: 690 V, front indicator



| Model | |
|--|------------------------------------|
| Product brand name | SETRON |
| Product designation | SITOR fuse link |
| Design of the product | With slotted blade contacts |
| Design of an identification indicator | front indicator |
| Design of the switching contact | With blade contacts, silver-plated |
| Design of the fuse link | SITOR, LV HRC design |
| General technical data | |
| Size of fuse system / acc. to DIN EN 60269-1 | NH2 |
| Operating class of the fuse link | gR |
| Varying load factor (WL) | 1 |
| Supply voltage | |
| Type of voltage | AC |
| Current / at AC / rated value | 500 A |
| Supply voltage | |
| • at AC / rated value | 690 V |
| Switching capacity | |
| Switching capacity current | |

- acc. to IEC 60947-2 / rated value

100 kA

Dissipation

Power loss [W] 65 W

Power loss [W]

- for rated value of the current / at AC / in hot operating state / per pole
- maximum

65 W

65 W

Product details

Product description Not non-interchangeable

Mechanical Design

Mounting position Any, preferably vertical

Environmental conditions

Ambient temperature -20 ... +50 °C

Environmental category -20 to +50 at 95% relative humidity

Certificates

Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F

F

General Product Approval

**Declaration of Con-
formity**

other



CCC



UR



EG-Konf.

[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NE1334-3>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NE1334-3>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NE1334-3

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



