

Contactor size S00, 3-pole AC-3 4 kW/400 V Screw terminal Screw terminal Auxiliary switch 22 E (2 NO + 2 NC) Overall width 45 mm 42 V DC !!! Phased-out product !!! Successor is SIRIUS 3RT201 or 3TG10



Figure similar

Product designation	Miniature contactor
Product type designation	3TF2
<b>General technical data</b>	
Size of contactor	0
Protection class IP	
• on the front	IP20
Reference code acc. to DIN EN 81346-2	Q
<b>Main circuit</b>	
Number of poles for main current circuit	3
Number of NO contacts for main contacts	3
Number of NC contacts for main contacts	0
Operating current	
• at AC-3	
— at 400 V rated value	9 A
• at AC-4 at 400 V rated value	2.6 A
Operating power	
• at AC-1	

- at 400 V rated value
- at AC-3
  - at 400 V rated value
  - at AC-4 at 400 V rated value

10 kW

4 kW

1 150 W

#### Control circuit/ Control

<b>Type of voltage of the control supply voltage</b>	DC
<b>Control supply voltage at DC</b>	
• rated value	42 V
<b>Control version of the switch operating mechanism</b>	conventional

#### Auxiliary circuit

<b>Number of NC contacts for auxiliary contacts</b>	
• instantaneous contact	2
<b>Number of NO contacts for auxiliary contacts</b>	
• instantaneous contact	2

#### Installation/ mounting/ dimensions

<b>Mounting type</b>	screw and snap-on mounting onto 35 mm standard mounting rail according to DIN EN 50022
• Side-by-side mounting	Yes
<b>Height</b>	48 mm
<b>Width</b>	45 mm
<b>Depth</b>	96 mm

#### Connections/ Terminals

<b>Type of electrical connection</b>	
• for main current circuit	screw-type terminals
• for auxiliary and control current circuit	screw-type terminals

#### Certificates/ approvals

General Product Approval	Functional Safety/Safety of Machinery	Declaration of Conformity
--------------------------	---------------------------------------	---------------------------



[Type Examination Certificate](#)



Declaration of Conformity	Test Certificates	Marine / Shipping	other
---------------------------	-------------------	-------------------	-------

[Miscellaneous](#)

[Special Test Certificate](#)

[Miscellaneous](#)

[Type Test Certificates/Test Report](#)



[Environmental Confirmations](#)

other	Railway
-------	---------

[Confirmation](#)

[Special Test Certificate](#)

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

[www.siemens.com/sirius/catalogs](http://www.siemens.com/sirius/catalogs)

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3TF2222-0BD4>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3TF2222-0BD4>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3TF2222-0BD4>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3TF2222-0BD4&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3TF2222-0BD4&lang=en)

**Characteristic: Tripping characteristics, I<sup>t</sup>, Let-through current**

<https://support.industry.siemens.com/cs/ww/en/ps/3TF2222-0BD4/char>

**Further characteristics (e.g. electrical endurance, switching frequency)**

<http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3TF2222-0BD4&objecttype=14&gridview=view1>

last modified:

09/12/2019