

Electronic motor control unit Values at 55 °C Standard:
 80 A Inside-delta: 156 A 200-460 V AC, 115 V AC
 Attention, not generally available, customer-specific product!

General technical data

Product brand name		SIRIUS
Product feature		No
<ul style="list-style-type: none"> integrated bypass contact system 		No
Product function		Yes
<ul style="list-style-type: none"> motor overload protection 		Yes
<ul style="list-style-type: none"> Evaluation of thermistor motor protection 		No
Reference code acc. to DIN EN 61346-2		Q

Power Electronics

Operating voltage at standard circuit rated value	V	200 ... 460
--	---	-------------

Ambient conditions

(derating temperature)	°C	40
-------------------------------	----	----

Certificates/approvals

General Product Approval	Test Certificates	other
--------------------------	-------------------	-------



[Special Test Certificate](#)

[Confirmation](#)

Further information

Simulation Tool for Soft Starters (STS)

<https://support.industry.siemens.com/cs/ww/en/view/101494917>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW3346-0EC34>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW3346-0EC34>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RW3346-0EC34>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RW3346-0EC34&lang=en



last modified:

09/11/2019