

SITOR fuse link, with slotted blade contacts, NH2, In: 710 A, aR, Un AC: 900 V, front indicator



Model	
Product brand name	SETRON
Product designation	SITOR fuse link
Design of the product	With slotted blade contacts
Design of an identification indicator	front indicator
Design of the switching contact	With blade contacts, silver-plated
Design of the fuse link	SITOR, LV HRC design
General technical data	
Size of fuse system / acc. to DIN EN 60269-1	NH2
Operating class of the fuse link	aR
Varying load factor (WL)	1
Supply voltage	
Type of voltage	AC
Current / at AC / rated value	710 A
Supply voltage	
• at AC / rated value	900 V
Switching capacity	
Switching capacity current	

- acc. to IEC 60947-2 / rated value

100 kA

### Dissipation

Power loss [W] 105 W

Power loss [W]

- for rated value of the current / at AC / in hot operating state / per pole
- maximum

105 W

105 W

### Product details

Product description Not non-interchangeable

### Mechanical Design

Mounting position Any, preferably vertical

### Environmental conditions

Ambient temperature -20 ... +50 °C

Environmental category -20 to +50 at 95% relative humidity

### Certificates

Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F

F

**General Product Approval**

**Declaration of Con-  
formity**

**other**



CCC



UR



EG-Konf.

[Miscellaneous](#)

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NE3337-8>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3NE3337-8>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NE3337-8](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NE3337-8)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



