

MINIZED, Switch disconnecter with Fuse, D02, 2-pole, In: 63 A, Un AC: 400 V



Model	
Product brand name	MINIZED
Product designation	Switch disconnectors with fuses
General technical data	
Number of poles	2
Size of fuse system / acc. to DIN EN 60269-1	D02
Overvoltage category	4
Voltage	
Surge voltage resistance / rated value	6 kV
Supply voltage	
Current / at AC / rated value	63 A
Operating voltage / at AC / rated value	400 V
Protection class	
Protection class IP	IP20, with connected conductors
Dissipation	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	5 W

## Product details

Product feature / sealable Yes

## Connections

Tightening torque / with screw-type terminals 2.5 ... 3 N·m

## Mechanical Design

Height	70 mm
Width	54 mm
Depth	90 mm
Mounting position	any, preferably vertical
Net weight	276 g

## Certificates

Reference code

- acc. to DIN EN 61346-2 F
- acc. to DIN EN 81346-2 F

General Product Approval	Declaration of Conformity	Test Certificates	Shipping Approval	other
--------------------------	---------------------------	-------------------	-------------------	-------



VDE



EG-Konf.

[Type Test Certificates/Test Report](#)



GL

[Miscellaneous](#)

## Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SG7123>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/5SG7123>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SG7123](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG7123)

**CAx-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



