

NEOZED, fuse base, D03, 1-pole, 100 A, Un AC: 400 V, Un DC: 250 V, without cover



Figure similar

Model	
Product brand name	NEOZED
Product designation	Fuse base
Design of the product	NEOZED fuse base installation
version	Ceramic fuse base without cover
Product variations	Without cover
General technical data	
Number of poles	1
Size of fuse system / acc. to DIN EN 60269-1	D03
Supply voltage	
Operating voltage / rated value	400 V
Dissipation	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	2.5 W
Main circuit	
Operating current / rated value	100 A

## Product details

Product component / Cover	No
---------------------------	----

## Mechanical Design

Height	86 mm
Width	44.9 mm
Depth	44 mm
Mounting type	DIN rail
Net weight	204 g
Material / of D fuse base	porcelain

## Certificates

Reference code	
• acc. to DIN EN 61346-2	F
• acc. to DIN EN 81346-2	F

**Declaration of Con-  
formity**

**Test Certificates**



EG-Konf.

[Special Test Certificate](#)

[Type Test  
Certificates/Test Report](#)

[Miscellaneous](#)

## Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SG1812>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/5SG1812>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SG1812](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG1812)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

