

MINIZED, fuse switch disconnecter, D01, 2-pole, 1P+N, In: 16 A, Un
AC: 230 V



Model	
Product brand name	MINIZED
Product designation	Fuse switch disconnecter
General technical data	
Number of poles	2
Number of poles / Note	1P+N
Size of fuse system / acc. to DIN EN 60269-1	D01
Overvoltage category	4
Voltage	
Surge voltage resistance / rated value	6 kV
Supply voltage	
Current / at AC / rated value	16 A
Operating voltage / at AC / rated value	230 V
Protection class	
Protection class IP	IP20, with connected conductors
Dissipation	

Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	0.2 W
--	-------

Product details

Product feature / sealable	Yes
----------------------------	-----

Connections

Tightening torque / with screw-type terminals	2.5 ... 3 N·m
---	---------------

Mechanical Design

Height	70 mm
Width	36 mm
Depth	88 mm
Mounting position	any, preferably vertical
Net weight	135 g

Certificates

Reference code	
<ul style="list-style-type: none"> • acc. to DIN EN 61346-2 • acc. to DIN EN 81346-2 	<p>F</p> <p>F</p>

General Product Approval	Declaration of Conformity
--------------------------	---------------------------



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SG7651-0KK16>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SG7651-0KK16>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG7651-0KK16

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

