

MINIZED, fuse switch disconnecter, D01, 4-pole, 3P+N, In: 16 A, Un  
AC: 400 V



Model	
Product brand name	MINIZED
Product designation	Fuse switch disconnecter
General technical data	
Number of poles	4
Number of poles / Note	3P+N
Size of fuse system / acc. to DIN EN 60269-1	D01
Overvoltage category	4
Voltage	
Surge voltage resistance / rated value	6 kV
Supply voltage	
Current / at AC / rated value	16 A
Operating voltage / at AC / rated value	400 V
Protection class	
Protection class IP	IP20, with connected conductors
Dissipation	

Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	0.4 W
--	-------

### Product details

Product feature / sealable	Yes
----------------------------	-----

### Connections

Tightening torque / with screw-type terminals	2.5 ... 3 N·m
---	---------------

### Mechanical Design

Height	70 mm
Width	108 mm
Depth	88 mm
Mounting position	any, preferably vertical
Net weight	270 g

### Certificates

Reference code	
<ul style="list-style-type: none"> <li>• acc. to DIN EN 61346-2</li> <li>• acc. to DIN EN 81346-2</li> </ul>	<p>F</p> <p>F</p>

<b>General Product Approval</b>	<b>Declaration of Conformity</b>
---------------------------------	----------------------------------



### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SG7661-0KK16>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/5SG7661-0KK16>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SG7661-0KK16](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG7661-0KK16)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

