

RCBO, 6 kA, 1P+N, type A, 30 mA, B char., In: 6 A, Un AC: 230 V



Model	
Product brand name	SENTRON
Product designation	RCBO
Design of the product	Instantaneous
General technical data	
Number of poles	2
Number of poles / Note	1P+N
Number of poles / with protection	1
Tripping characteristic class	B
circuit-breaker / Design	5SU1
Mechanical service life (switching cycles) / typical	10 000
Oversvoltage category	III
Voltage	
Surge current resistance / at (8/20) $\mu$ s	1 kA
Supply voltage	
Type of voltage	AC
Current / at AC / rated value	6 A
Supply voltage	

• for testing equipment / minimum	195 V
Supply voltage frequency / rated value	50 Hz
<b>Protection class</b>	
Protection class IP	IP20, if the distribution board is installed, with connected conductors
<b>Switching capacity</b>	
Breaking capacity short-circuit current (I <sub>cn</sub> ) / according to EN 61009-1 / rated value	6 kA
Switching capacity current	
• acc. to EN 60898 / rated value	6 kA
• acc. to IEC 60947-2 / rated value	25 kA
Rated residual switching capacity (I <sub>Δm</sub> ) / according to IEC 61009-1	6 kA
Energy limiting class	3
<b>Dissipation</b>	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	2.7 W
<b>Current</b>	
Tripping residual current / rated value	30 mA
Tripping residual / rated value / derated current	
• at 30 Cel	6 A
• at 40 Cel	5.7 A
• at 45 Cel	5.58 A
• at 50 Cel	5.4 A
• at 55 Cel	5.22 A
• at 60 Cel	5.1 A
• at 65 Cel	4.86 A
• at 70 Cel	4.62 A
Type of fault current	A
<b>Product details</b>	
Product function / neutral conductor switching	Yes
Product feature / Touch protection	Yes
Product feature	
• halogen-free	Yes
• silicon-free	Yes
<b>Connections</b>	
• Connectable conductor cross-section	
— solid	0.75 ... 35 mm <sup>2</sup>
— stranded	0.75 ... 35 mm <sup>2</sup>
• Connectable conductor cross-section / finely stranded / with core end processing	0.75 ... 25 mm <sup>2</sup>

Tightening torque / with screw-type terminals	2.5 ... 3 N·m
Position / of power supply cord	Either top or bottom

### Mechanical Design

Height	90 mm
Width	36 mm
Depth	77 mm
Installation depth	70 mm
Number of width units	2
Mounting position	any
Net weight	255 g

### Environmental conditions

Influence of the surrounding temperature	Max. 95% humidity
Ambient temperature	-25 ... +55 °C
• during storage	-40 ... +75 °C

### Certificates

Reference code	
• acc. to DIN EN 61346-2	F
• acc. to DIN EN 81346-2	F

### General Product Approval

### Declaration of Conformity



CCC



IMQ



VDE

[Miscellaneous](#)



RCM



EG-Konf.

Test Certificates	other	Railway
<a href="#">Special Test Certificate</a>	<a href="#">Miscellaneous</a>	<a href="#">Miscellaneous</a>
		<a href="#">Vibration and Shock</a>
		<a href="#">Confirmation</a>

### Further information

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

#### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SU1356-6KK06>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SU1356-6KK06>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SU1356-6KK06](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SU1356-6KK06)

#### CAX-Online-Generator

<http://www.siemens.com/cax>

#### Tender specifications

<http://www.siemens.com/specifications>



