

RC unit for 5SL4, 3-pole, type A, In: 40 A, 30 mA, Un AC: 400 V



Model	
Product brand name	SENTRON
Product designation	RC unit
Design of the product	Instantaneous
Product variations	for 5SL4
General technical data	
Number of poles	3
Size of installation devices / acc. to DIN 43880	1
Protection against electrical shock	Finger and back-of-hand safe
circuit-breaker / Design	5SM2
Mechanical service life (switching cycles) / typical	10 000
Switching function / short-term delayed	No
Overvoltage category	III
Supply voltage	
Current / at AC / rated value	40 A
<ul style="list-style-type: none"> <li>• Supply voltage / at AC / rated value</li> <li>• Supply voltage / for testing equipment / minimum</li> </ul>	<p>400 V</p> <p>195 V</p>

• rated value

50 Hz

### Protection class

Protection class IP	IP20, if the distribution board is installed, with connected conductors
---------------------	---

### Dissipation

Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	3.6 W
---	-------

### Current

Tripping residual current / rated value	30 mA
---	-------

Tripping residual / rated value / derated current

• at 40 Cel	37.2 A
• at 45 Cel	37.2 A
• at 50 Cel	36 A
• at 55 Cel	34.8 A
• at 60 Cel	34 A
• at 65 Cel	33.2 A
• at 70 Cel	32 A

Type of fault current	A
-----------------------	---

Surge current resistance / rated value	1 kA
--	------

Operating frequency	50Hz
---------------------	------

### Product details

Product feature / silicon-free	Yes
--------------------------------	-----

Product extension / can be installed / supplementary devices	Yes
--	-----

### Connections

Connectable conductor cross-section	
• solid	1.5 ... 25 mm <sup>2</sup>
• stranded	1.5 ... 25 mm <sup>2</sup>

Tightening torque / with screw-type terminals	2.5 ... 3 N·m
---	---------------

Position / of power supply cord	top or bottom
---------------------------------	---------------

### Mechanical Design

Height	90 mm
--------	-------

Width	105 mm
-------	--------

Depth	70 mm
-------	-------

Installation depth	70 mm
--------------------	-------

Number of width units	3
-----------------------	---

Mounting type	DIN rail (REG)
---------------	----------------

Mounting position	any
-------------------	-----

Net weight	320 g
------------	-------

### Environmental conditions

Ambient temperature

- during storage

-25 ... +45 °C

-40 ... +75 °C

## Certificates

General Product Approval

Declaration of  
Conformity

other



CCC



VDE

[Miscellaneous](#)



EG-Konf.

[Miscellaneous](#)

## Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SM2333-6>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/5SM2333-6>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SM2333-6](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SM2333-6)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



