

NEOZED, fuse base, D02, 3-pole, 63 A, Un AC: 400 V, Un DC: 250 V, for Busbar system 8US 60 mm



Model	
Product brand name	NEOZED
Product designation	Fuse base
Design of the product	NEOZED bus-mounting bases
Product variations	For 60 mm 8US busbar system
General technical data	
Number of poles	3
Size of fuse system / acc. to DIN EN 60269-1	D02
Supply voltage	
Operating voltage / rated value	400 V
Dissipation	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	3 W
Main circuit	
Operating current / rated value	63 A
Product details	
Product component / Cover	Yes

## Mechanical Design

Height	200 mm
Width	36 mm
Depth	43 mm
Mounting type	Busbar system
Net weight	165 g
Material / of D fuse base	plastic

## Certificates

### Reference code

- acc. to DIN EN 61346-2 F
- acc. to DIN EN 81346-2 F

## Declaration of Conformity



EG-Konf.

## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SG6207>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SG6207>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SG6207](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG6207)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>

