

1

CHARACTERISTICS

Ambient temperature	-20 ÷ 80 °C
Fluid	filtered air, with or without lubrication
Working pressure	1,5 ÷ 10 bar
End-caps	die-cast aluminium
Barrel	anodized aluminium
Piston	aluminium
Guide slide	acetalic resin
Piston rod	chromium-plated steel, stainless steel upon request
Piston seal	NBR
Guide bush for piston rod	acetalic resin
Shock absorber seals	NBR
Cushionings	pneumatic adjustable (UNIVER Original standard supplied)
Magnet	standard supplied
Other available versions	tandem, two-position tandem, opposed tandem, with common piston rod (upon request)



CODIFICATION KEY

R	M	3	0	0	0	3	2	0	0	2	5	
1	2	3	4	5	6							

1 Series	2 Type	3 Version
RM = Ø 16÷100 mm - ISO 21287 Compact Cylinders	3 = Stainless steel male piston rod 4 = Chromium-plated steel male piston rod Upon request 1 = Stainless steel female piston rod (Ø40÷100) 2 = Chromium-plated steel female piston rod (Ø 40÷100)	00 = D.A. Standard version 01 = D.A. Through piston rod 20 = D.A. Long piston (Ø32÷63) 60 = S.A. Retracted piston rod 70 = S.A. Extended piston rod

D.A. = Double acting
S.A. = Single acting

4 Bore (mm)	5 Stroke (mm)	6 Option
016 = Ø16 050 = Ø50 020 = Ø20 063 = Ø63 025 = Ø25 080 = Ø80 032 = Ø32 100 = Ø100 040 = Ø40	Single acting 0005 - 0010 (Ø16÷25) 0005 - 0010 - 0015 - 0020 - 0025 (Ø32÷100) Double acting 0005 - 0010 - 0015 - 0020 - 0025 - 0030 - 0040 0050 - 0060 - 0080	Max standard stroke 0040 (Ø16) 0050 (Ø20-25) 0080 (Ø32÷63) H = Hollow piston rod only for through piston rod versions without flange

For high temperature applications please contact our Sales Office

FIXING ELEMENTS AND ACCESSORIES

Ø	Female fork with clips	Articulated self-lubricating fork	Fork with axially mounted articulated pin	Fork with angle mounted articulated pin	Floating joint	Centering adaptor ring	Female rear hinge with pin	Counter hinge 90° (CETOP)	Counter hinge 90°	Counter hinge 90° (CNOMO)	Narrow female hinge with pin
16						-					
20	MF-15012	MF-17012	MF-22016	MF-23012	MF-24012	-	-	-	-	-	-
25	MF-15020	MF-17020	MF-22020	MF-23020	MF-24020	-	-	-	-	-	-
32	KF-15032	KF-17032	KF-22032	KF-23032	KF-24032	RSF-09032	KF-10032A	KF-19032CTA	KF-19032	KF-19032CN	KF-10032AS
40	KF-15032	KF-17032	KF-22032	KF-23032	KF-24032	RSF-09040	KF-10040A	KF-19040CTA	KF-19040	KF-1904050CN	KF-10040AS
50	KF-15040	KF-17040	KF-22040	KF-23040	KF-24040	RSF-09050	KF-10050A	KF-19050CTA	KF-19050	KF-19040050CN	KF-10050AS
63	KF-15040	KF-17040	KF-22040	KF-23040	KF-24040	RSF-09063	KF-10063A	KF-19063CTA	KF-19063	KF-19063080CN	KF-10063AS
80	KF-15080	KF-17080	KF-22080	KF-23080	KF-24080	RSF-09080	KF-10080A	KF-19080CTA	KF-19080	KF-19063080CN	KF-10080AS
100	KF-15080	KF-17080	KF-22080	KF-23080	KF-24080	RSF-09100	KF-10100A	KF-19100CTA	KF-19100	KF-19100125CN	KF-10100AS
Ø	Articulated counter hinge	Articulated rear male hinge	Rear male hinge	Front/rear flange	Angle bracket	Front/rear hinge with floating pin	Hinge support	ISO intermediate hinge	DF sensor and DHF covering strip	Cable clamping for DF sensor	
16											
20	-	-	-	-	-	-	-	-	DF DHF-0020100	DF-001	
25	-	-	-	-	-	-	-				
32	KF-190325C	KF-11032S	KF-11032	KF-12032	KF-13032	KF-14032AP	KF-41032	KDF-14032			
40	KF-190405C	KF-11040S	KF-11040	KF-12040	KF-13040	KF-14040AP	KF-41040050	RPF-14040			
50	KF-190505C	KF-11050S	KF-11050	KF-12050	KF-13050	KF-14050AP	KF-41040050	RPF-14050			
63	KF-190635C	KF-11063S	KF-11063	KF-12063	KF-13063	KF-14063AP	KF-41063080	RPF-14063			
80	KF-190805C	KF-11080S	KF-11080	KF-12080	KF-13080	KF-14080AP	KF-41063080	KDF-14080			
100	KF-191005C	KF-11100S	KF-11100	KF-12100	KF-13100	KF-14100AP	KF-41100125	KDF-14100			