Wall-mount Remote Control for brand switches – 2 channels

Product ref.: 152000A0





Supply voltage	230 V/50 Hz
Current consumption	10 mA max.
Standby power consumption	0.2 W
Degree of protection	IP20
Cable type and cross section	rigid and flexible cable, 0.75 - 1.5 mm
Installation	only in normal commercial switch boxes (device boxes) in accordance with DIN 49073-1
Ambient temperature	5 to 35 °C
Dimensions (W x H x D)	71 x 71 x 37 mm
Weight	47 g
Radio frequency band	868.0-868.6 MHz 869.4-869.65 MHz
Typ. open area RF range	240 m











Product features

- Mains-operated wall-mount remote control with two channels for controlling Homematic IP devices and functions
- Controls connected Homematic IP actuators and pluggable switches to switch lights on or off, for example
- Activation of the eco mode for all radiators or the panic light at the push of a button
- Compact design for installation in standard flush-mounting hoves
- Can also be integrated into existing switches by making use of existing frames and rockers
- With the appropriate adapter, the device can be integrated into the most popular switch designs of leading manufacturers: Busch-Jaeger, Gira, Merten, Berker, Jung, Düwi, Kopp
- A neutral conductor is required for installation
- For operation, the Homematic IP Access Point in connection with the Homematic IP app (no recurring costs), the Homematic Central Control Unit CCU2 or an appropriate partner solution is required

Logistical data

Product reference	152000A0
EAN code	4047976520008
Short description	HmIP-BRC2
Packing unit	90
Packing dimensions	122 x 112 x 48 mm
Weight incl. packaging	122.0 g

Package contents

Homematic IP Wall-mount Remote Control for brand switches – 2 channels

Screws 3.2 x 15 mm (2x)

Screws 3.2 x 25 mm (2x)

User manual