


Datenblatt



**UNLESS OTHERWISE SPECIFIED
GENERAL TOLERANCES**
 0.5~6 = ±0.2
 >6~30 = ±0.4
 >30~120 = ±0.6

Specification

1. Rating : 3A 12VDC
2. Withstanding voltage
AC 500V, 60Hz for 1 minute
3. Insulation resistance(initial)
100M ohm(min.) at 500V DC
4. Contact resistance(initial)
30m ohm(max.) at AC 100mA(max) 1 KHz
5. Insertion & Extraction force
Initial : 0.3 to 3.0 Kgs
After life test : 0.2 to 3.0 Kgs
6. Life test(20-30 cycle/minute)
5,000 cycles unloading