

**Klippon POK (polyester empty enclosure)
KLIPPON COPL 254012/16**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Brass earthing plates (Earth Continuity Plate) for
the Klippon® POK enclosure**

In order to provide internal earthing (especially for the Ex version) earth continuity plates in an angled design are available for the Klippon® POK enclosure.

These internal earth continuity plates are for the usage of metal glands and the design of EMC applications; they offer enhanced protection and are available separately.

General ordering data

Type	KLIPPON COPL 254012/16
Order No.	1391040000
Version	Klippon POK (polyester empty enclosure), Earthing plate, Width: 85.5 mm, Material: Brass, polished, untreated
GTIN (EAN)	4050118191141
Qty.	1 pc(s).

**Klippon POK (polyester empty enclosure)
KLIPPON COPL 254012/16**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Length	567 mm	Length (inches)	22.323 inch
Width	85.5 mm	Width (inches)	3.366 inch
Wall thickness, max.	0.8 mm	Wall thickness, min.	0.8 mm
Net weight	326 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General information

Material thickness	0.8 mm	Material	Brass
Surface finish	polished, untreated		

General information on accessories

Material	Brass	Material thickness	0.8 mm
Surface finish	polished, untreated		

Classifications

ETIM 5.0	EC002623	ETIM 6.0	EC002623
eClass 6.2	27-18-92-64	eClass 7.1	27-18-92-64
eClass 8.1	27-18-92-64	eClass 9.0	27-18-28-14
eClass 9.1	27-18-92-64		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP