

## Testing tools VT LCL

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



- Reacts from a distance of 4 mm
- No current flow necessary thanks to capacitive method
- Detects concealed broken wires with a tolerance of just a few millimetres
- Detects voltage-conducting wires in sockets, cable reels, distributors, etc.
- Display: visual or both visual and acoustic
- including a flashlight function with the VT LCL

### General ordering data

Type	VT LCL
Order No.	<a href="#">2436670000</a>
Version	Cable detector
GTIN (EAN)	4050118450033
Qty.	1 pc(s).

**Testing tools  
VT LCL**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	155 mm	Width (inches)	6.102 inch
Height	25 mm	Height (inches)	0.984 inch
Depth	23 mm	Depth (inches)	0.906 inch
Weight	60 g	Net weight	55.3 g

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**Measuring and testing devices**

Battery type	1.5 V type AAA battery	DC voltage measuring range	1000 V
Display	Visual & acoustic	Measuring range category	CAT IV 1000 V
Protection degree	IP65	Rated voltage, max.	1000 V AC
Rated voltage, min.	12 V AC	Tested and approved according to	DIN EN 61010-1, DIN EN 61326

**Classifications**

ETIM 3.0	EC000494	ETIM 4.0	EC000494
ETIM 5.0	EC000494	ETIM 6.0	EC000494
eClass 6.2	27-20-03-08	eClass 7.1	27-20-03-08
eClass 8.1	27-20-03-08	eClass 9.0	27-20-03-08
eClass 9.1	27-20-03-08		

**Approvals**

ROHS Conform

**Downloads**

User Documentation [Manual](#)