SAI Active
SAIEND CAN-M12 5P A-COD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Weidmüller offers a wide range of tools and accessories for sensor-actuator cabling.

General ordering data

Type	SAIEND CAN-M12 5P A-COD
Order No.	1784760000
Version	Protected component assemblies, SAI Active, Accessories, Sensor/Actuator plug-in connector
GTIN (EAN)	4032248191840
Qty.	1 pc(s).

SAI Active
SAIEND CAN-M12 5P A-COD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	12.8 g

Temperatures

Operating temperature, max.	85 °C	Operating temperature, min.	-25 °C
Operating temperature	-25 °C...85 °C	Storage temperature	

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1

General data

Material	metal	No. of poles	5
Protection degree	IP67, IP68		

Classifications

ETIM 4.0	EC002556	ETIM 5.0	EC002556
ETIM 6.0	EC000448	UNSPSC	30-21-18-10
eClass 5.1	27-26-07-01	eClass 6.2	27-24-26-92
eClass 7.1	27-24-26-92	eClass 8.1	27-24-26-92
eClass 9.0	19-07-04-03	eClass 9.1	19-17-01-90

Approvals

Approvals	EAC
ROHS	Conform

Downloads

Brochure/Catalogue	CAT U_REMOTE 16/17 EN CAT 8 SAI 15/16 EN FL FIELDWIRING EN


Weidmüller

SAI Active
SAIEND CAN-M12 5P A-COD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Dimensioned drawing



Pole scheme

