

ESG ESG 6.6/20 BHZ 5.00 SDR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from the following manufacturers:

- Siemens
- Télémecanique
- ABB
- Beckhoff
- Lumberg
- Tags for all-purpose usage; self-adhesive or clip-on tags, depending on the type

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

Please note that these markers are not intended for printing with the SpeedMarking laser.

General ordering data

Type	ESG 6.6/20 BHZ 5.00 SDR
Order No.	1221520000
Version	ESG, Device markers x 20 mm, PA 66, Colour: To customer specification
GTIN (EAN)	4050118005066
Qty.	40 pc(s).
compatible printer	1324380000

Data sheet

ESG ESG 6.6/20 BHZ 5.00 SDR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	20 mm	Width (inches)	0.787 inch
Height	6.6 mm	Height (inches)	0.26 inch
Depth	0.8 mm	Depth (inches)	0.031 inch
Net weight	0.33 g		

General data

Application/manufacturer	BHZ, ACT 20	Colour	To customer specification
Halogen	No	Material	PA 66
Operating temperature range	-40...100 °C	Printed characters	Based on customer requirements (Please send M-Print PRO file)
Printing method	MC Laser	UL 94 flammability rating	V-2
Width	20 mm		

Classifications

ETIM 4.0	EC001288	ETIM 5.0	EC001288
ETIM 6.0	EC001288	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29	eClass 8.1	27-14-91-03
eClass 9.0	27-40-06-29	eClass 9.1	27-40-06-29

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
------------------	------------------------------