
SAI-M23-SE-L-4/4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Pinning



The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

General ordering data

Type	SAI-M23-SE-L-4/4
Order No.	1170380000
Version	Sensor/Actuator plug-in connector, Insert
GTIN (EAN)	4032248962518
Qty.	1 pc(s).

SAI-M23-SE-L-4/4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	7 g

Temperatures

Operating temperature, max.	125 °C	Operating temperature, min.	-40 °C

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1

Standards

Certificate No. (UR)	E344862

General data

Coding	none	Conductor O.D.	-
Connection thread	M23	Contact number / diameter	4 x 1 mm + 4 x 2 mm
Design	Male	Fire behaviour	V-0
Housing main material	Thermoplastic polyamide PA 6, PBT	Insulation strength	> 10^{13} Ω
No. of poles	8	Plugging cycles	> 1000
Rated current	1 mm Kontakt = 8 A, 2 mm Kontakt = 28 A	Rated voltage (text)	1 mm Kontakt = 300 V, 2 mm Kontakt = 600 V
Type of connection	Crimp connection		

Classifications

ETIM 5.0	EC002635	ETIM 6.0	EC000438
eClass 6.2	27-06-91-90	eClass 7.1	27-06-91-90
eClass 8.1	27-06-91-90	eClass 9.1	27-44-02-05

Product information

Product information	Enclosures, inserts and crimp contacts need to be ordered separately.

Approvals

Approvals	
ROHS	Conform

Downloads


Brochure/Catalogue	CAT 8 SAI 15/16 EN FL FIELDWIRING EN

SAI-M23-SE-L-4/4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Dimensioned drawing



Technical data

No. of poles		5 + PE	4/4	
Number of contacts		6	4	4
Contact-ø	mm	2	1	2

4 times 1-mm male and 4 times 2-mm male