

**VG S (standard stainless steel cable gland)
VGM50-SS 68 KB 22-32**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



This cable gland series is made from stainless steel and is well suited for industrial applications requiring IP68 protection. Its excellent resistance against seawater and impacts make it ideal for use in harsh conditions.

General ordering data

Type	VGM50-SS 68 KB 22-32
Order No.	1009900000
Version	VG S (standard stainless steel cable gland), Cable glands, M 50, 9 mm, OD min. 22 - OD max. 32 mm, Stainless steel 1.4305 (303)
GTIN (EAN)	4032248714728
Qty.	5 pc(s).

VG S (standard stainless steel cable gland) VGM50-SS 68 KB 22-32

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	55 mm	Length (inches)	2.165 inch
Net weight	254 g		

General information

AF size 1	50 mm	AF size 2	55 mm
Cable glands	metric	Clamp insert	Polyamide 6
External thread	M 50	Length of thread	9 mm
Material	Stainless steel 1.4305 (303)	O-Ring	NBR
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Outer cable diameter, max.	32 mm	Outer cable diameter, min.	22 mm
Pitch of thread	1.5 mm	Protection degree	IP69K, IP68 - 5 bar (30 min.)
Seal insert	CR	Torque for cap nut, max.	45 Nm
Torque for cap nut, min.	35 Nm	Torque for connecting adapter, max.	50 Nm
Torque for connecting adapter, min.	60 Nm		

Classifications

ETIM 4.0	EC002625	ETIM 5.0	EC002625
ETIM 6.0	EC000441	eClass 6.2	27-18-92-34
eClass 7.1	27-18-92-34	eClass 8.1	27-18-92-34
eClass 9.0	27-14-44-32	eClass 9.1	27-14-44-32

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP