

**MICROSERIES
MAS DC/DC select**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Product image



Do not use product for new developments



When used for industrial monitoring applications, sensors can record ambience conditions. Sensor signals are used within the process to continually track changes to the area being monitored. Both digital and analogue signals can occur.

Normally an electrical voltage or current value is produced which corresponds proportionally to the physical variables that are being monitored. Analogue signal processing is required when automation processes have to constantly maintain or reach defined conditions. This is particularly significant for process automation applications. Standardised electrical signals are typically used for process engineering. Analogue standardised currents / voltage 0(4)...20 mA/ 0...10 V have established themselves as physical measurement and control variables.

Weidmüller meets the ever increasing challenges of automation and offers a product portfolio tailored to the requirements of handling sensor signals in analogue signal processing

The analogue signal processing products can be used universally in combination with other Weidmüller products and in combination among each other. Their

electrical and mechanical design is such that they require only minimal wiring efforts.

Housing types and wire-connection methods matched to the respective application facilitate the universal use in process and industrial automation applications.

The product line includes the following functions:

- Isolating transformers, supply isolators and signal converters for DC standard signals
- Temperature measuring transducers for resistance thermometers and thermocouples,

General ordering data

| | |
|------------|------------------|
| Type | MAS DC/DC select |
| Order no. | 4032248252442 |
| Version | 1 |
| GTIN (EAN) | 4032248252442 |
| Qty. | 1 pc(s). |

- displays
- calibration devices

The products mentioned are available as pure signal converters / isolation transducers, 2-way/3-way isolators, supply isolators, passive isolators or as trip amplifiers.

**MICROSERIES
MAS DC/DC select**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data
Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Length | 88 mm | Length (inches) | 3.465 inch |
| Width | 6.1 mm | Width (inches) | 0.24 inch |
| Depth | 97.8 mm | Depth (inches) | 3.85 inch |
| Net weight | 52 g | | |

Temperatures

| | | | |
|-----------------------------|--------------|-----------------------------|----------------|
| Operating temperature, max. | 55 °C | Operating temperature, min. | 0 °C |
| Storage temperature, max. | 85 °C | Storage temperature, min. | -20 °C |
| Operating temperature | 0 °C...55 °C | Storage temperature | -20 °C...85 °C |

Probability of failure

| | |
|------|-----------|
| MTTF | 440 Years |
|------|-----------|

Environmental Product Compliance

| | |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

Rated data UL

| | |
|-------------------------|---------|
| Certificate No. (cURus) | E175400 |
|-------------------------|---------|

Input

| | | | |
|---------------------------|-----------------|---------------|--|
| Number of inputs | 1 | Input voltage | 0...10 V |
| Input resistance, voltage | 100 k Ω | Input current | 0...20 mA, 4...20 mA |
| Input resistance, current | $\leq 5 \Omega$ | Voltage drop | < 0.1 V @ I _{IN} = 20 mA (current input) |

Output

| | | | |
|------------------------|---------------------------|---------------------------|-------------------|
| Number of outputs | 1 | Output voltage, note | 0...10 V |
| Output current | 0...20 mA, 4...20 mA | Cut-off frequency (-3 dB) | > 100 Hz |
| load impedance voltage | $\geq 10 \text{ k}\Omega$ | load impedance current | $\leq 500 \Omega$ |

General data

| | | | |
|---|---------------------|-------------------------|---|
| Current-carrying capacity of cross-connect. | $\leq 20 \text{ A}$ | Galvanic isolation | 3-way isolator |
| Input/Output | configurable | Power consumption | ca. 0.6 W |
| Rail | TS 35 | Temperature coefficient | $\leq 150 \text{ ppm/K}$ of final value |
| Voltage supply | 24 V DC $\pm 15 \%$ | | |

Insulation coordination

| | | | |
|---|----------------------------|---|----------------------------|
| EMC standards | DIN EN 61326 | Galvanic isolation | 3-way isolator |
| Insulation voltage | 500 V _{eff} / 1 s | Insulation voltage input or output/rail | 500 V _{eff} / 1 s |
| Insulation voltage input or output/supply | 500 V _{eff} / 1 s | Pollution severity | 2 |
| Rated voltage | 50 V | Surge voltage category | II |

Data sheet

**MICROSERIES
MAS DC/DC select**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Connection data

| | | | |
|----------------------|---------------------|----------------------------------|---------------------|
| Type of connection | Screw connection | Clamping range, rated connection | 2.5 mm ² |
| Clamping range, min. | 0.5 mm ² | Clamping range, max. | 2.5 mm ² |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC001774 | ETIM 4.0 | EC002653 |
| ETIM 5.0 | EC002653 | ETIM 6.0 | EC002653 |
| eClass 6.2 | 27-21-01-20 | eClass 7.1 | 27-21-01-20 |
| eClass 8.1 | 27-21-01-20 | eClass 9.0 | 27-21-01-20 |
| eClass 9.1 | 27-21-01-90 | | |

Approvals

Approvals



ROHS Conform

Downloads

| | |
|---|---|
| Approval/Certificate/Document of Conformity | Declaration of Conformity |
| Engineering Data | EPLAN, WSCAD |
| User Documentation | Instruction sheet |

Data sheet

**MICROSERIES
MAS DC/DC select**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Electric symbol

