

TM
VT-TM 1/18 TWIN HF**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



TM/TF Twin double-sided labelling: 0.22 – 2.5 mm².

Twin sleeves enable double-sided marking of a conductor.

The sleeves can hold two TM-I 18 tags so that, for example, the input and output designations of a cable can be read at one position. The transparent, halogen-free sleeves can be used on conductors with an outside diameter of 1.3 to 4.0 mm.

General ordering data

Type	VT-TM 1/18 TWIN HF
Order No.	1891790000
Version	TM, Socket x 5 mm, Polyethylene LD, Colour: Transparent, Conductor O.D.: 2.4 - 4 mm
GTIN (EAN)	4032248504534
Qty.	1,000 pc(s).

TM
VT-TM 1/18 TWIN HF
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data
Dimensions and weights

Width	5 mm	Width (inches)	0.197 inch
Height	18 mm	Height (inches)	0.709 inch
Depth	12 mm	Depth (inches)	0.472 inch
Net weight	0.15 g		

General data

Colour	Transparent	Halogen	No
Material	Polyethylene LD	Operating temperature range	-40...80 °C
Recommended industries	Transportation, Machinery	Type of printing	neutral
UL 94 flammability rating	HB	Width	5 mm

Conductor and cable markers

Conductor O.D.	2.4 - 4 mm	Conductor O.D., max.	4 mm
Conductor O.D., min.	2.4 mm	Conductor cross-section, max.	2.5 mm ²
Conductor cross-section, min.	1.5 mm ²	Halogen	No

Classifications

ETIM 3.0	EC001530	ETIM 4.0	EC001530
ETIM 5.0	EC001530	ETIM 6.0	EC001530
UNSPSC	44-12-17-08	eClass 5.1	27-14-91-03
eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-03
eClass 8.1	27-14-91-03	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN , WSCAD , Zuken E3.S
------------------	--