

CableLine
CLI M 2-4 WS/SW 7 CD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Similar to illustration

CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections.

Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm²
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

General ordering data

Type	CLI M 2-4 WS/SW 7 CD
Order No.	1568300007
Version	CableLine, Conductor and cable markers, 10 - 317 mm, 4 x 11.3 mm, white
GTIN (EAN)	4032248450817
Qty.	500 pc(s).
Alternative product	1912830000

CableLine
CLI M 2-4 WS/SW 7 CD
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data
Dimensions and weights

Width	11.3 mm
Height	4 mm
Depth	3 mm
Net weight	0.146 g

Width (inches)	0.445 inch
Height (inches)	0.157 inch
Depth (inches)	0.118 inch

General data

Colour	white
--------	-------

Halogen	Yes
---------	-----

Material colour according to resistance code	9
--	---

Orientation of print	horizontal
----------------------	------------

Printing	7
----------	---

Recommended industries	Process, Machinery
------------------------	--------------------

UL 94 flammability rating	V-0
---------------------------	-----

Width	11.3 mm
-------	---------

Colour of printing	black
--------------------	-------

Material	PVC, soft, without Cadmium
----------	----------------------------

Operating temperature range	-30...80 °C
-----------------------------	-------------

Printed characters	Numbers
--------------------	---------

Printing method	hot-embossing
-----------------	---------------

Type of printing	Standard
------------------	----------

Version	CD
---------	----

Conductor and cable markers

Conductor O.D.	10 - 317 mm
----------------	-------------

Conductor O.D., min.	10 mm
----------------------	-------

Conductor cross-section, min.	16 mm ²
-------------------------------	--------------------

Conductor O.D., max.	317 mm
----------------------	--------

Conductor cross-section, max.	500 mm ²
-------------------------------	---------------------

Halogen	Yes
---------	-----

Classifications

ETIM 3.0	EC001530
----------	----------

ETIM 5.0	EC001530
----------	----------

UNSPSC	44-12-17-08
--------	-------------

eClass 6.2	27-40-04-01
------------	-------------

eClass 8.1	27-14-91-03
------------	-------------

eClass 9.1	27-40-04-01
------------	-------------

ETIM 4.0	EC001288
----------	----------

ETIM 6.0	EC001530
----------	----------

eClass 5.1	27-14-91-03
------------	-------------

eClass 7.1	27-14-91-29
------------	-------------

eClass 9.0	27-40-04-01
------------	-------------

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
------------------	------------------------------

Product Change Notification	PCN CableLine_DE PCN CableLine_EN
-----------------------------	--

CableLine **CLI M 2-4 WS/SW 7 CD**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings



Similar to illustration