RIGOL
Innovation or nothing

DG900 Series

Function/Arbitrary Waveform Generator

- Unique SiFi II (Signal Fidelity II) technology: generate the arbitrary waveforms point by point; recover the signal without distortion; sample rate accurate and adjustable; jitter of all the output waveforms (including Sine, Pulse, etc.) as low as 200 ps
- 16 Mpts memory depth per channel for arbitrary waveforms
- Standard dual-channel with the same performance, equivalentto two independent signal sources
- High frequency stability: ±1 ppm; low phase noise: -105 dBc/Hz
- Built-in high-order harmonic generator (at most 8-order harmonics)
- Built-in 7 digits/s, 240 MHz bandwidth full featured frequency counter
- Up to 160 built-in arbitrary waveforms, covering the common signals in engineering application, medical electronics, auto electronics, math processing, and other various fields
- Sample rate up to 250 MSa/s, vertical resolution 16 bits
- Arbitrary waveform sequence editing function available; arbitrary waveforms also can be generated through the PC software
- Various analog and digital modulation functions: AM, FM, PM, ASK, FSK, PSK, and PWM.
- Standard waveform combine function, capable of outputting specified waveforms combined with the basic waveforms
- Standard channel tracking function, when enabled, all the parameters of both channels are updated based on users' configurations
- USB Host&Device interface (standard); USB-GPIB function supported
- 4.3" TFT color touch screen
- RS232, PRBS, and Dualtone outputs supported

Design Features

Unique SiFi II Technology

Generate the arbitrary waveforms points by points without distorting the signals. In comparison with the last generation of the SiFi technology, SiFi II has added multiple filters, supporting the dynamic adjustment of the edge time.

Touch–enabled UI Design

Provide brand new UI operation experience, supporting the tap and drag operation gestures. You can also use the keyboard to complete the parameter settings.









Advanced Function Output

Support PRBS and RS232 pattern output and local Sequence editing.

100MHz Bandwidth White Gaussian Noise



Natural Heat Dissipation Without Fan
0 dB Operating Noise

The brand new heat dissipation structure desgin has undergone the strict thermal simulation test to ensure the steady operation of the instrument in a complex environment.

DG900 Series
Function/Arbitrary Waveform Generator

Dimensions: W×H×D = 237.4 mm × 97 mm × 268 mm Weight: 1.75 kg (Package Excluded)

Function Interface

Dual-channel with the same performance





SiFi II — Arbitrary waveform function with the unique SiFi II technology



160 built-in arbitrary waveforms



Burst function



Various analog and digital modulation functions





Sweep function

Standard harmonic generator function



Dualtone function



PRBS function



RS232 function



Sequence function





Waveform combine function



Standard 7 digits/s, 240 MHz bandwidth frequency counter



Channel and system setting

File management function

Specifications

Unless otherwise specified, all the specifications can be guaranteed when the following two conditions are met.

- The signal generator is within the calibration period.
- The signal generator has been running ceaselessly for over 30 minutes under the specified operating temperature (23℃ ± 5℃).

All the specifications are guaranteed except the parameters marked with "Typical".

DG900 series specifications

Model	DG952	DG972	DG992
Channel	2	2	2
Max. Frequency	50 MHz	70 MHz	100 MHz
Sample Rate	250 MSa/s		

Waveform	
Basic Waveforms	Sine, Square, Ramp, Pulse, Noise, DC, Dual-tone
Advanced Waveforms	PRBS, RS232, Sequence
Built-in Arbitrary Waveforms	160 types of waveforms, including Sinc, Exponential Rise, Exponential Fall, ECG, Gauss, HaverSine, Lorentz, etc.

Frequency Characteristics			
Sine	1 μHz to 50 MHz	1 μHz to 70 MHz	1 μHz to 100 MHz
Square	1 μHz to 15 MHz	1 μHz to 20 MHz	1 μHz to 25 MHz
Ramp	1 μHz to 1.5 MHz	1 μHz to 1.5 MHz	1 μHz to 2 MHz
Pulse	1 μHz to 15 MHz	1 μHz to 20 MHz	1 μHz to 25 MHz
Harmonic	1 μHz to 20 MHz	1 μHz to 20 MHz	1 μHz to 25 MHz
PRBS	2 kbps to 40 Mbps	2 kbps to 50 Mbps	2 kbps to 60 Mbps
Dual-tone	1 μHz to 20 MHz	1 μHz to 20 MHz	1 μHz to 20 MHz
RS232	baud rate range: 9600, 14400, 19200, 38400, 57600, 115200, 128000, 230400		
Sequence	2 k to 60 MSa/s		
Noise (-3 dB)	100 MHz bandwidth		
Arbitrary Waveform	1 μHz to 15 MHz	1 μHz to 20 MHz	1 μHz to 20 MHz
Resolution	1 μHz		
Accuracy	±(1 ppm of the setting value + 10 pHz), 18℃ to 28℃		

Sine Wave Spectrum Purity	
Harmonic Distortion	Typical[1] DC to 10 MHz (included): <-55 dBc 10 MHz to 20 MHz (included): <-50 dBc 20 MHz to 40 MHz (included): <-40 dBc >40 MHz: <-35 dBc
Total Harmonic Distortion[1]	<0.075% (10 Hz to 20 kHz)
Spurious (non-harmonic)	Typical[1] ≤10 MHz: <-60 dBc >10 MHz: <-60dBc + 6dB/octave
Phase Noise	Typical (0 dBm, 10 kHz offset) 10 MHz: <-105 dBc/Hz

Signal Characteristics	
Square	
Rise/Fall Time	Typical (1 Vpp, 1 kHz) ≤9 ns
Overshoot	Typical (100 kHz, 1 Vpp) ≤5%
Duty	0.01% to 99.99% (limited by the current frequency setting)
Non-symmetry	1% of the period + 4 ns
Jitter (rms)	Typical (1 Vpp) ≤5 MHz: 2 ppm of the period + 200 ps >5 MHz: 200 ps
Ramp	
Linearity	≤1% of peak output (typical, 1 kHz, 1 VPP, 100% symmetry)

Symmetry	0% to 100%
Pulse	
Pulse	16 ns to 1000 ks (limited by the current frequency setting)
Duty	0.001% to 99.999% (limited by the current frequency setting)
Rising/Falling Edge	≥8ns (limited by the current frequency setting and pulse width setting)
Overshoot	Typical (1 Vpp, 1 kHz) ≤5%
Jitter (rms)	Typical (1 Vpp) ≤5 MHz: 2 ppm of the period + 200 ps >5 MHz: 200 ps
Arbitrary Waveform Sequence	
Waveform Length	16 Mpts
Vertical Resolution	16 bits
Sample Rate	Interpolation filter: 10 Sa/s to 60 MSa/s Step filter: 2k Sa/s to 50 MSa/s Smooth filter: 2k Sa/s to 50 MSa/s
Min Rise/Fall Time	Interpolation filter: ≥8 ns Step filter: 3.0/sample rate Smooth filter: 1.0/sample rate
Jitter (rms)	Typical (1 Vpp) Interpolation filter: 200 ps Step filter: <5 ps Smooth filter: <5 ps
Overshoot	Typical (1 Vpp) ≤5%
Harmonic Output	
Harmonic Order	≤8
Harmonic Type	Even Harmonic, Odd Harmonic, Order Harmonic, User
Harmonic Amplitude	The amplitude of each order of the harmonic can be set.
Harmonic Phase	The phase of each order of harmonic can be set.

Output Characteristics	
Amplitude (into 50 Ω)	
Range	≤10 MHz: 1.0 mVpp to 10 Vpp ≤30 MHz: 1.0 mVpp to 5.0 Vpp ≤60 MHz: 1.0 mVpp to 2.5 Vpp >60 MHz: 1.0 mVpp to 1 Vpp
Accuracy	Typical (1 kHz sine, 0 V offset, >10 mVpp, auto) ±(1% of the setting value) ± 5 mV
Flatness	Typical (Sine, 1 Vpp) ≤5 MHz: ±0.1 dB ≤15 MHz: ±0.2 dB ≤25 MHz: ±0.3 dB ≤40MHz: ±0.5 dB >40 MHz: ±1 dB
Unit	Vpp, Vrms, dBm
Resolution	0.1 mVpp or 4 digits
Offset (into 50 Ω)	
Range(Peak ac+dc)	±5 Vpk ac+dc
Accuracy	±(1% of the setting value + 5 mV + 1% of the amplitude)
Waveform Output	
Output Impedance	50 Ω (typical)
Protection	Short-circuit protection, automatically disable the waveform output when overload occurs

Modulation Characteristics	
Modulation Type	AM, FM, PM, ASK, FSK, PSK, PWM
AM	
Carrier Waveform	Sine, Square, Ramp, Arb
Source	Internal/External
Modulating Waveform	Sine, Square, Ramp, Noise, Arb
Modulation Depth	0% to 120%
Modulation Frequency	2 mHz to 1 MHz

FM	
Carrier Waveform	Sine, Square, Ramp, Arb
Source	Internal/External
Modulating Waveform	Sine, Square, Ramp, Noise, Arb
Modulation Frequency	2 mHz to 1 MHz
PM	
Carrier Waveform	Sine, Square, Ramp, Arb
Source	Internal/External
Modulating Waveform	Sine, Square, Ramp, Noise, Arb
Phase Deviation	0° to 360°
Modulation Frequency	2 mHz to 1 MHz
ASK	
Carrier Waveform	Sine, Square, Ramp, Arb
Source	Internal/External
Modulating Waveform	Square with 50% duty cycle
Key Frequency	2 mHz to 1 MHz
FSK	
Carrier Waveform	Sine, Square, Ramp, Arb
Source	Internal/External
Modulating Waveform	Square with 50% duty cycle
Key Frequency	2 mHz to 1 MHz
PSK	
Carrier Waveform	Sine, Square, Ramp, Arb
Source	Internal/External
Modulating Waveform	Square with 50% duty cycle
Key Frequency	2 mHz to 1 MHz
PWM	
Carrier Waveform	Pulse
Source	Internal/External
Modulating Waveform	Sine, Square, Ramp, Noise, Arb
Width Deviation	0% to 100% of the pulse width
Modulation Frequency	2 mHz to 1 MHz
External Modulation Input	
Input Range	AM, PM, FM: 75 mVRMS to ±5 (Vac+dc) ASK, PSK, FSK: standard 5 V TTL
Input Bandwidth	50 kHz
Input Impedance	10 kΩ

Burst Characteristics			
Carrier Waveform	Sine, Square, Ramp, Pulse, Noise, Arb, PRBS, RS232, Sequence (except DC, dual-tone, and Harmonic)		
Carrier Frequency	2 mHz to 10 MH	2 mHz to 20 MHz	2 mHz to 30 MHz
Burst Count	1 to 1,000,000 or Infinite		
Internal Period	1 μs to 500 s		
Gated Source	External Trigger		
Source	Internal, External, Manual		
Trigger Delay	0 ns to 100 s		

Sweep Characteristics	
Carrier Waveform	Sine, Square, Ramp, Arb
Type	Linear, Log, and Step
Orientation	Up/Down
Start/Stop Frequency	Same as the upper/lower limit of the corresponding carrier frequency
Sweep Time	1 ms to 500 s
Hold/Return Time	0 ms to 500 s
Source	Internal, External, Manual
Marker	Falling edge of the sync signal (programmable)

Frequency Counter	
Measurement Function	Frequency, Period, Positive/Negative Pulse Width, Duty Cycle

Frequency Resolution	7 digits/s (Gate Time = 1 s)		
Frequency Range	1 μHz to 240 MHz		
Period Measurement	Measurement Range	4 ns to 1,000 ks	
Voltage Range and Sensitivity (non-modulating signal)			
DC Coupling	DC Offset Range	±1.5 Vdc	
	1 μHz to 100 MHz	50 mVRMS to ±2.5 (Vac+dc)	
	100 MHz to 240 MHz	100 mVRMS to ±2.5 (Vac+dc)	
AC Coupling	1 μHz to 100 MHz	50 mVRMS to ±2.5 Vpp	
	100 MHz to 240 MHz	100 mVRMS to ±2.5 Vpp	
Pulse Width and Duty Cycle Measurement			
Frequency and Amplitude Ranges	1 μHz to 25 MHz	50 mVRMS to ±2.5 (Vac+dc)	DC Coupling
Pulse Width	Min. Pulse Width	≥20 ns	
	Pulse Width Resolution	5 ns	
Duty	Measurement Range (display)	0% to 100%	
Input Characteristics			
Input Signal Range	Breakdown Voltage	±7 (Vac+dc)	Input Impedance = 1 MΩ
Input Adjustment	Coupling Mode	AC	DC
	High Frequency Rejection	On: Input Bandwidth = 150 kHz; Off: Input Bandwidth = 240 MHz	
Input Trigger	Trigger Level Range	-2.5 V to +2.5 V	
	Trigger Sensitivity Range	High, Low	
GateTime	1 ms	1.048 ms	
	10 ms	8.389 ms	
	100 ms	134.218 ms	
	1 s	1.074 s	
	10 s	8.590 s	
	>10 s	>8.590 s	

Trigger Characteristics	
Trig Input	
Level	TTL-compatible
Slope	Rising or falling (selectable)
Pulse Width	>100 ns
Latency	Sweep: <100 ns (typical) Burst: <350 ns (typical)
Trigger Output	
Level	TTL-compatible
Pulse Width	>60 ns (typical)
Max. Frequency	1 MHz

Two-channel Characteristics - Phase Offset	
Range	0° to 360°
Waveform Phase Resolution	0.03°

Reference Clock	
External Reference Input	
Lock Range	10 MHz ± 50 Hz
Level	250 mVpp to 5 Vpp
Lock Time	<2 s
Input Impedance(Typical)	1 kΩ, AC coupling
Internal Reference Output	
Frequency	10 MHz ± 50 Hz
Level	3.3 Vpp
Output Impedance(Typical)	50 Ω, AC coupling

Synchronous Output	
Level	TTL-compatible

Impedance	50 Ω, nominal value
Overvoltage Protection	
Occurred when: The instrument amplitude setting is greater than 3.2 Vpp or the output AC+DC is greater than $\|1.6V_{DC}\|$ and the input voltage is greater than ±12 × (1 ± 5%)V (<10 kHz).Disruptive discharge voltage: ±5(Vac + dc). The instrument amplitude setting is smaller than or equal to 3.2 Vpp or the output AC+DC is smaller than $\|1.6V_{DC}\|$ and the input voltage is greater than ±2.6 × (1 ± 5%)V (<10 kHz).Disruptive discharge voltage: ±18(Vac + dc).	
Overcurrent Protection	
Occurred when: the current is greater than ±240 mA.	

Programming Time	
Configuration Changes	USB
Function Change	10 ms
Amplitude Change	5 ms
Frequency Change	5 ms

General Specifications		
Power Supply		
Power Voltage	100 V to 127 V (45 Hz to 440 Hz) 100 V to 240 V (45 Hz to 65Hz)	
Power Consumption	Lower than 30 W	
Display		
Type	4.3-inch TFT LCD touch screen	
Resolution	480 horizontal × RGB × 272 vertical resolution	
Color	16 M	
Environment		
Temperature Range	Operating: 0℃ to 45℃ Non-operating: -40℃ to 60℃	
Cooling Method	Fan cooled	
Humidity Range	Below 30℃: ≤95%RH 30℃ to 40℃: ≤75%RH 40℃ to 50℃: ≤45%RH	
Altitude	Operating: below 3,000 meters Non-operating: below 15,000 meters	
Mechanical Characteristics		
Dimensions (W×H×D)	238 mm × 97 mm × 266.6 mm	
Weight	Package excluded: 1.75 kg Package included: 2.85 kg	
Interface	USB Host, USB Device, and USB-GPIB	
IP Protection	IP2X	
Calibration Interval	1 year (recommended)	
Certification Information		
EMC	Compliant with EN61326-1:2006	
	IEC 61000-3-2:2000	±4.0 kV (Contact Discharge) ±4.0 kV (Air Discharge)
	IEC 61000-4-3:2002	3 V/m (80 MHz to 1 GHz); 3 V/m (1.4 GHz to 2 GHz); 1 V/m (2.0 GHz to 2.7 GHz)
	IEC 61000-4-4:2004	1kV power line
	IEC 61000-4-5:2001	0.5 kV (phase-to-neutral voltage); 0.5 kV (phase-to-earth voltage); 1 kV (neutral-to-earth voltage)
	IEC 61000-4-6:2003	3 V, 0.15 MHz to 80 MHz
	IEC 61000-4-11:2004	Voltage dip: 0% UT during half cycle 0% UT during 1 cycle 70% UT during 25 cycles Short interruption: 0% UT during 1 cycle
Electrical Safety	complies with USA: UL 61010-1:2012, Canada: CAN/CSA-C22.2 No. 61010-1-2012 EN 61010-1:2010,	

Note[1]: 0 dBm output, DC offset 0, impedance 50 Ω.

Options and Accessories

	Description	Order No
Model	DG952 (50MHz, Dual-channel)	DG952
	DG972 (70MHz, Dual-channel)	DG972
	DG992 (100MHz, Dual-channel)	DG992
Standard Accessories	1 Power Cord conforming to the standard of the destination country	-
	1 USB Cable	CB-USBA-USBB-FF-150
	1 BNC Cable	CB-BNC-BNC-MM-100
	1 Quick Guide	-
	1 Product Warranty Card	-
Optional Accessories	40 dB Attenuator	RA5040K
	USB-GPIB Interface Converter	USB-GPIB-L

HEADQUARTER

RIGOL TECHNOLOGIES, INC.
No.8 Keling Road, New District,Suzhou,
JiangSu,P.R.China
Tel:+86-400620002
Email:info@rigol.com

EUROPE

RIGOL TECHNOLOGIES EU GmbH
Lindbergh str. 4
82178 Puchheim
Germany
Tel: 0049-89/89418950
Email: info-europe@rigol.com

NORTH AMERICA

RIGOL TECHNOLOGIES, USA INC.
8140 SW Nimbus Ave.
Beaverton, OR 97008
Tel: 877-4-**RIGOL**-1
Fax: 877-4-**RIGOL**-1
Email: info@rigol.com

JAPAN

RIGOL TECHNOLOGIES JAPAN, LLC
MJ Bldg. 3F, 1-7-4 Minato, Chuou-ku,
Tokyo, Japan 104-0043
Tel: +81-3-6262-8932
Fax: +81-3-6262-8933
Email: info-japan@rigol.com

DSB10100-2018-07