

# Enterprise Capacity 3.5 HDD

## Data Sheet

### Capacity-Optimized Enterprise Hard Drive for Bulk-Data Applications

- 8TB, 3.5-inch enterprise drive with industry-leading 6-disk technology,<sup>1</sup> resulting in 33% more storage in the same storage slot
- Advanced Write Caching feature to utilize enhanced algorithms, resulting in the industry's highest nearline storage workload performance efficiencies—100% performance improvement in random writes over last-generation drive
- Widely accepted, proven ninth-generation conventional perpendicular recording technology for reliable access to unstructured data in bulk storage applications
- 12Gb/s SAS and SATA 6Gb/s interfaces in industry-standard advanced formats for easy integration into replicated and RAID multi-drive storage servers and systems
- State-of-the-art cache, on-the-fly error-correction algorithms, super parity and end-to-end SAS-based data integrity for accurate data storage
- Industry-leading rotational vibration tolerance design helps ensure consistent performance in dense multi-drive systems
- Engineered for 24x7 workloads of 550TB/yr—10x that of desktop drives
- Robust performance with dual processors, ramp load technology, top-cover-attached motor and humidity sensor for optimum performance in all chassis
- Seagate Secure™ Self-Encrypting Drive featuring Instant Secure Erase for cost-saving drive retirement and secure data-at-rest protection<sup>2</sup>
- Seagate SeaTools™ diagnostic software to provide drive self-tests ensuring unnecessary downtime and maximizing TCO

### Best-Fit Applications

- Hyperscale applications/cloud data centers with replicated storage
- Massive scale-out data centers and big data analytics
- High-capacity density RAID storage
- Mainstream enterprise external storage arrays (SAN, NAS, DAS)
- Distributed file systems, including Hadoop and Ceph
- Enterprise backup and restore—D2D, virtual tape
- Centralized surveillance

<sup>1</sup> Seagate recommends validating your configuration with your HBA/RAID controller manufacturer to ensure full capacity capabilities.

<sup>2</sup> Self-Encrypting Drives (SED) are not available in all models or countries. May require TCG-compliant host or controller support.





# Enterprise Capacity 3.5 HDD



Specifications	SATA 6Gb/s	12Gb/s SAS
	8TB <sup>1,2</sup>	8TB <sup>1,2</sup>
Standard Model Number (4K Native)	ST8000NM0045	ST8000NM0065
Standard Model Number (512 Emulation)	ST8000NM0055	ST8000NM0075
SED Model Number (4K Native)	ST8000NM0115 <sup>3</sup>	ST8000NM0095 <sup>3</sup>
SED Model Number (512 Emulation)	ST8000NM0105 <sup>3</sup>	ST8000NM0085 <sup>3</sup>
<b>Features</b>		
Protection Information (T10 DIF)	—	Yes
Humidity Sensor	Yes	Yes
Super Parity	Yes	Yes
Low Halogen	Yes	Yes
PowerChoice™ Technology	Yes	Yes
PowerBalance™ Technology	Yes (512 Emulation models only)	Yes (512 Emulation models only)
Cache, Multisegmented (MB)	256	256
Advanced Write Caching (2M Internal NOR Flash)	Yes	Yes
<b>Reliability/Data Integrity</b>		
Mean Time Between Failures (MTBF, hours)	2.0M	2.0M
Reliability Rating @ Full 24x7 Operation (AFR)	0.44%	0.44%
Nonrecoverable Read Errors per Bits Read	1 sector per 10E15	1 sector per 10E15
Power-On Hours per Year	8760 (24x7)	8760 (24x7)
Sector Size (Bytes per Logical Sector)	512 and 4096	512, 520, 528 and 4096
Limited Warranty (years)	5	5
<b>Performance</b>		
Spindle Speed (RPM)	7200	7200
Interface Access Speed (Gb/s)	6.0, 3.0, 1.5	12.0, 6.0, 3.0
Random Read/Write—16QD WCE (IOPS)	164/342	164/342
Max. Sustained Transfer Rate OD (MB/s)	up to 237	up to 237
Average Latency (ms)	4.16	4.16
Interface Ports	Single	Dual
Rotational Vibration @ 1500 Hz (rad/s <sup>2</sup> )	12.5	12.5
<b>Power Consumption</b>		
Idle Power, Average (W)	9	9
Typical Operating, Random Read (W)	<10	<10
Power Supply Requirements	+12V and +5V	+12V and +5V
<b>Environmental</b>		
Temperature, Operating (°C)	5 to 60	5 to 60
Vibration, Nonoperating: 10Hz to 500Hz (Grms)	5.0	4.9
Shock, Operating, 2ms (Read/Write) (Gs)	70/40	70/40
Shock, Nonoperating, 1ms and 2ms (Gs)	300	300
<b>Physical</b>		
Height (in/mm, max) <sup>4</sup>	1.028/26.1	1.028/26.1
Width (in/mm, max) <sup>4</sup>	4.010/101.85	4.010/101.85
Depth (in/mm, max) <sup>4</sup>	5.787/147.0	5.787/147.0
Weight (lb/g)	1.720/780	1.720/780
Carton Unit Quantity	20	20
Cartons per Pallet	40	40
Cartons per Layer	8	8

1 One gigabyte, or GB, equals one billion bytes and one terabyte, to TB, equals one trillion bytes when referring to drive capacity.

2 Seagate recommends validating your configuration with your HBA/RAID controller manufacturer to ensure full capacity capabilities.

3 Self-Encrypting Drives (SED) are not available in all models or countries. May require TCG-compliant host or controller support.

4 These base deck dimensions conform to the Small Form Factor Standard (SFF-8201) found at [www.sffcommittee.org](http://www.sffcommittee.org). For connector-related dimensions, see SFF-8223.



seagate.com

AMERICAS  
ASIA/PACIFIC  
EUROPE, MIDDLE EAST AND AFRICA

Seagate Technology LLC 10200 South De Anza Boulevard, Cupertino, California 95014, United States, 408-658-1000  
Seagate Singapore International Headquarters Pte. Ltd. 7000 Ang Mo Kio Avenue 5, Singapore 569877, 65-6485-3888  
Seagate Technology SAS 16-18, rue du Dôme, 92100 Boulogne-Billancourt, France, 33 1-4186 10 00