

**Industrial Ethernet
IE-BHD-V04P**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



PushPull plug-in connector according to IEC
61076-3-106 ver.4 (IEC24702), plastic, empty housing

General ordering data

Type	IE-BHD-V04P
Order No.	2027660000
Version	Device flange, Variant 4 to IEC 61076-3-106, IP67
GTIN (EAN)	4050118406061
Qty.	200 pc(s).

**Industrial Ethernet
IE-BHD-V04P**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Wall thickness, max.	3.5 mm	Net weight	0.01 g
----------------------	--------	------------	--------

Temperatures

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Operating temperature	-40 °C...70 °C	Storage temperature	
Installation temperature			

General data

Colour	Miscellaneous	Housing main material	PA UL 94 V0
Protection degree	IP67	Seal material	NBR
UL 94 flammability rating	V-0		

Standards

Connector standard	IEC 61076-3-106 Var. 4	Certificate no. (cULus)	E471884
--------------------	------------------------	-------------------------	---------

Classifications

ETIM 6.0	EC001031	eClass 6.2	27-25-05-04
eClass 9.0	27-18-27-02	eClass 9.1	27-18-27-02

Approvals

Approvals



ROHS Conform

Downloads


Brochure/Catalogue	CAT 9 IETH 15/16 EN MB FREECONTACT EN FL FIELDWIRING EN PI PROFINET CABLING EN
User Documentation	Mounting_instruction_2027660000-IE-BHD-V04P.pdf MAN IE GUIDE DE MAN IE GUIDE EN

**Industrial Ethernet
IE-BHD-V04P**


Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Drawings

Drawing



Installation cut-out



max. Paneldicke: 3,5mm
 max. Panel thickness: 3,5 mm

M2,5 Gewinde darf kein Sackloch sein
 M2.5 threads mustn't go through the panel