

**CableLine**  
**CLI C 2-4 WS/SW 3 MP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

**General ordering data**

|                     |                                                                    |
|---------------------|--------------------------------------------------------------------|
| Type                | CLI C 2-4 WS/SW 3 MP                                               |
| Order No.           | <a href="#">0251310003</a>                                         |
| Version             | CableLine, Conductor and cable markers, 4 - 10 mm, 4 x 7 mm, white |
| GTIN (EAN)          | 4032248007981                                                      |
| Qty.                | 100 pc(s).                                                         |
| Alternative product | <a href="#">1568269999</a>                                         |

**CableLine**  
**CLI C 2-4 WS/SW 3 MP**
**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data**
**Dimensions and weights**

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Width      | 7 mm   | Width (inches)  | 0.276 inch |
| Height     | 4 mm   | Height (inches) | 0.157 inch |
| Depth      | 8 mm   | Depth (inches)  | 0.315 inch |
| Net weight | 0.13 g |                 |            |

**General data**

|                             |                            |                                              |                    |
|-----------------------------|----------------------------|----------------------------------------------|--------------------|
| Colour                      | white                      | Colour of printing                           | black              |
| Halogen                     | Yes                        | Insulation cross-section, max.               | 10 mm              |
| Material                    | PVC, soft, without Cadmium | Material colour according to resistance code | 9                  |
| Operating temperature range | -30...80 °C                | Orientation of print                         | horizontal         |
| Printed characters          | Numbers                    | Printing                                     | 3                  |
| Printing method             | hot-embossing              | Recommended industries                       | Process, Machinery |
| Type of printing            | Standard                   | UL 94 flammability rating                    | V-0                |
| Version                     | MultiPack                  | Width                                        | 7 mm               |

**Conductor and cable markers**

|                               |                     |                               |                    |
|-------------------------------|---------------------|-------------------------------|--------------------|
| Conductor O.D.                | 4 - 10 mm           | Conductor O.D., max.          | 10 mm              |
| Conductor O.D., min.          | 4 mm                | Conductor cross-section, max. | 16 mm <sup>2</sup> |
| Conductor cross-section, min. | 2.5 mm <sup>2</sup> | Halogen                       | Yes                |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001530    | ETIM 4.0   | EC001288    |
| ETIM 5.0   | EC001530    | ETIM 6.0   | EC001530    |
| UNSPSC     | 44-12-17-08 | eClass 5.1 | 27-14-91-03 |
| eClass 6.2 | 27-40-04-01 | eClass 7.1 | 27-14-91-29 |
| eClass 8.1 | 27-14-91-03 | eClass 9.0 | 27-40-04-01 |
| eClass 9.1 | 27-40-04-01 |            |             |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                             |                                                                      |
|-----------------------------|----------------------------------------------------------------------|
| Engineering Data            | <a href="#">EPLAN, WSCAD</a>                                         |
| Product Change Notification | <a href="#">PCN CableLine_DE</a><br><a href="#">PCN CableLine_EN</a> |

### **CableLine** **CLI C 2-4 WS/SW 3 MP**

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



Similar to illustration