


Model No.: **GPCR123A**

Ultra+



Label Area


Unit : mm

Description	: Lithium Battery, CR123A
Chemical System	: Lithium Manganese Dioxide
Nominal Voltage	: 3.0 Volts
Nominal Capacity	: 1500mAh @ 10mA to 2.0V at 23°C
Dimensions	: $\varnothing 17$ mm x 34.5 mm
Terminals	: Flat, Recessed Negative Terminal
Jacket	: PVC Resin Label
Shelf Life	: Up to 10 years
Average Weight	: App. 16g
Max. Constant Current	: 1500mA
Max. Pulse Current	: 3500mA
Application	: Smoke Detector, Sensors, Home Security Products, Medical Equipment
Operating Temperature	: -40°C to +60°C
UL Standard	: UL1642 (File no. MH46184) UL2054 (File no. MH25972)
IEC Standard	: IEC60086-4
UN Standard	: UN38.3


Cross References:

IEC	GP	Panasonic	Energizer	Duracell
CR17345	CR123A	CR-123A	EL123AP	DL123A


900mA pulse discharge to 1.55V at 23°C & -20°C




1200mA pulse discharge to 1.3V at 23°C & -20°C



10mA continuous discharge to 2.0V at 23°C



1800mA pulse discharge to 1.8V at 23°C



The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.

www.gpbatteries.com