

TM
TM 7/18 HF/HB**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The TM sleeves contain no halogens and virtually no pollutants. The sleeves are equipped with the TM-I 12 or TM-I 18 tags. They cover a wide range of applications for cables and lines. This system has particularly proved its worth in traffic engineering. The slim design guarantees firm seating on the conductor.

- Halogen-free
- The slim design guarantees firm seating on the conductor
- TMX 18 for mounting with cable-ties (width 3.6 mm)

General ordering data

Type	TM 7/18 HF/HB
Order No.	1192770000
Version	TM, Socket x 28 mm, Polyethylene LD, Colour: Transparent, Conductor O.D.: 20 - 30 mm
GTIN (EAN)	4032248974818
Qty.	100 pc(s).

TM
TM 7/18 HF/HB

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data
Dimensions and weights

Width	28 mm	Width (inches)	1.102 inch
Height	18 mm	Height (inches)	0.709 inch
Depth	32.7 mm	Depth (inches)	1.287 inch
Net weight	1.44 g		

General data

Colour	Transparent	Halogen	No
Material	Polyethylene LD	Operating temperature range	-40...80 °C
Recommended industries	Transportation, Machinery	Type of printing	neutral
UL 94 flammability rating	HB	Width	28 mm

Conductor and cable markers

Conductor O.D.	20 - 30 mm	Conductor O.D., max.	30 mm
Conductor O.D., min.	20 mm	Halogen	No

Classifications

ETIM 3.0	EC001530	ETIM 4.0	EC001530
ETIM 5.0	EC001530	ETIM 6.0	EC001530
eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-03
eClass 8.1	27-14-91-03	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP