



7-Port Industrial USB 3.0 Hub

Seven USB 3.0 Type-A Ports, 20 kV ESD Protection, A/C, Bus and Terminal-Block Power Options, DIN Rail, Wall Mountable, Metal Housing, Screw-Lock Security

Part No.: [164405](#)

Fast, powerful SuperSpeed USB 3.0 performance in a multiport hub

The Manhattan 7-Port Industrial USB 3.0 Hub easily expands and secures your USB access in industrial environments and high traffic areas. Versatile, sturdy mounting options allow the hub to be secured to a wall, used on a desktop or added to a DIN rail. This hub creates more open connection points for USB 3.0 devices, such as external hard drives and printers. Built-in screw-lock ports offer security for cables and additional stability from vibrations in the surrounding environment. It is backward compatible with previous USB standards to provide flexibility for attached devices. The Manhattan 7-Port Industrial USB 3.0 Hub offers plug-and-play, hot-swap capabilities and data transfer speeds up to 5 Gbps.

Features:

- Provides seven SuperSpeed USB 3.0 ports for additional peripherals
- Supports data transfer rates up to 5 Gbps
- Rugged metal housing and screw-locking USB connections offer robust security in high-traffic areas and industrial environments
- Built-in rubber feet, detachable wall mounts and DIN-rail support provide multiple installation options
- AC, bus-powered and terminal-block power options with overcurrent and 20 kV ESD

For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

protection; does not support simultaneous use of terminal block and AC power

- Supports battery-charge specification 1.2 (BC 1.2)
- Backward compatible with all USB 2.0 and 1.1 devices
- Power and port-activation LED indicator
- Plug and Play
- Three-year warranty

Specifications:

Standards and Certifications

- USB 3.0
- FCC
- CE
- RoHS
- WEEE

Ports

- Transfer speeds: 12 Mbps / 480 Mbps / 5 Gbps
- Seven USB 3.0 type A
- One USB 3.0 type B
- 9 – 40 reverse polarity VDC port: 5.5 x 2.1 x 9.5 mm
- 9 – 40 reverse polarity VDC port, three-pin terminal block

Physical

- Dimensions: 15.8 x 3.2 x 8 cm (6.22 x 1.26 x 3.15 in)
- Weight: 0.33 kg (0.73 lbs.)
- USB 3.0 type-A to type-B cable: 1 m (3 ft.); screw-lock connector
- Housing: metal
- Detachable metal wall-mount brackets
- Detachable DIN-rail mount bracket
- LED power indicators: green

System Requirements

- Does not support simultaneous use of terminal block and A/C power
- USB-enabled PC or Mac system
- Windows XP/Vista/7/8.1/10 or Mac OS 9 or above
- Available USB port
- 32 W power adapter (recommended; a higher-power adapter can also be used)

Operating Environment

- Operation Temperature: 0 – 40°C (32 – 104°F)
- Storage Temperature: -20 – 60°C (-4 – 140°F)
- Humidity (noncondensing): 0 – 96%

Package Contents

- 7-Port Industrial USB 3.0 Hub
- USB cable

- One DIN-rail bracket
- Two wall-mount brackets
- 3-PIN Terminal Block
- Quick Instruction Guide



