

**Industrial Ethernet  
IE-C6FP8LD0035M40M40-D****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Assembled IE cables, patch cable Cabinet Line, Cat. 6,  
LSZH, grey

**General ordering data**

|            |                                                                                                                     |
|------------|---------------------------------------------------------------------------------------------------------------------|
| Type       | IE-C6FP8LD0035M40M40-D                                                                                              |
| Order No.  | <a href="#">1165940035</a>                                                                                          |
| Version    | Patch cable, RJ45 IP 20, RJ45 IP 20, Cat.6 <sub>A</sub> /<br>Class E <sub>A</sub> (ISO/IEC 11801 2010), LSZH, 3.5 m |
| GTIN (EAN) | 4050118159011                                                                                                       |
| Qty.       | 1 pc(s).                                                                                                            |

## Industrial Ethernet IE-C6FP8LD0035M40M40-D

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Dimensions and weights

|            |         |                          |            |
|------------|---------|--------------------------|------------|
| Length     | 3.5 m   | Length (inches)          | 0.138 inch |
| Net weight | 142.5 g | Insulation cross-section | 1.04 mm    |

### Temperatures

|                             |                |                             |                |
|-----------------------------|----------------|-----------------------------|----------------|
| Operating temperature, max. | 60 °C          | Operating temperature, min. | -20 °C         |
| Storage temperature, max.   | 60 °C          | Storage temperature, min.   | -20 °C         |
| Operating temperature       | -20 °C...60 °C | Storage temperature         | -20 °C...60 °C |
| Installation temperature    | 0 °C...50 °C   |                             |                |

### Environmental Product Compliance

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

### Electrical properties

|                                    |                            |                   |              |
|------------------------------------|----------------------------|-------------------|--------------|
| Current-carrying capacity at 50 °C | 1 A                        | Operating voltage | 48 V AC / DC |
| PoE / PoE+                         | conforming to IEEE 802.3at |                   |              |

### Standards

|                                                     |                                                                   |                    |                |
|-----------------------------------------------------|-------------------------------------------------------------------|--------------------|----------------|
| Application-specific communication cable facilities | ANSI / TIA / EIA-568-B.2-10, ISO / IEC 11801:2002, EN50173-1:2007 | Connector standard | IEC 60603-7-51 |
| Certificate no. (cULus)                             | E316369                                                           |                    |                |

### Cable structure

|                            |                                        |                                       |                                                            |
|----------------------------|----------------------------------------|---------------------------------------|------------------------------------------------------------|
| Copper diameter            | 0.43 mm                                | Strands                               | 7                                                          |
| Cross-section              | 4*2*AWG 27/7 - 4*2*0.1 mm <sup>2</sup> | Insulation                            | PE                                                         |
| Insulation cross-section   | 1.04 mm                                | No. of wires                          | 8                                                          |
| Arrangement of wire cores  | Twisted pair                           | Colour sequence or wires - wire pairs | white - blue, white - orange, white - green, white - brown |
| Shielding                  | S/FTP                                  | Complete shielding                    | Shielding braid made from copper wiring                    |
| Overlap of shielding braid | 60 %                                   | Material sheath                       | LSZH                                                       |
| Sheath diameter, min.      | 5.5 mm                                 | Sheath diameter, max.                 | 5.9 mm                                                     |

### Electrical properties of cable

|                                          |                                                    |                                     |                 |
|------------------------------------------|----------------------------------------------------|-------------------------------------|-----------------|
| Category                                 | Cat.6A / Class E <sub>A</sub> (ISO/IEC 11801 2010) | Operating voltage                   | 48 V AC / DC    |
| Operating voltage (UL rating)            | 30 V AC / 42.4 V DC                                | Test voltage: wire-wire-shield      | 750 V DC, 1 min |
| Characteristic impedance                 | 100 ± 15 Ω at 1–100 MHz                            | Deviation                           | 25 ns/100m      |
| Resistance differential                  | 5 %                                                | Capacity at 1 kHz                   | 46 nF/km        |
| Speed                                    | 10 GBit/s                                          | Coupling resistance at 10 MHz       | 5 mΩ/m          |
| Shield attenuation up to 1000 MHz        | 60 dB                                              | Coupling attenuation up to 1000 MHz | 80 dB           |
| Separating class according to EN 50174-2 | d                                                  |                                     |                 |

## Industrial Ethernet IE-C6FP8LD0035M40M40-D

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Mechanical and material properties of cable

|                                |                                        |                                 |                                              |
|--------------------------------|----------------------------------------|---------------------------------|----------------------------------------------|
| Min. bending radius, once only | 25 mm                                  | Min. bending radius, repetitive | 50 mm                                        |
| Speed                          | 10 GBit/s                              | Resistance to spread of flame   | in accordance with IEC 60332-1 / UL 1581 FT2 |
| Halogen                        | halogen-free, according to IEC 60754-2 |                                 |                                              |

### plug

|                |            |                 |            |
|----------------|------------|-----------------|------------|
| Connector left | RJ45 IP 20 | Connector right | RJ45 IP 20 |
|----------------|------------|-----------------|------------|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001262    | ETIM 5.0   | EC000748    |
| ETIM 6.0   | EC002599    | eClass 6.2 | 27-06-03-90 |
| eClass 7.1 | 27-06-03-90 | eClass 8.1 | 27-06-03-90 |
| eClass 9.0 | 27-06-03-08 | eClass 9.1 | 27-06-03-08 |

### Approvals

Approvals



ROHS

Conform

### Downloads

|                                             |                                                                                        |
|---------------------------------------------|----------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">DUXR.E316369</a>                                                           |
| Brochure/Catalogue                          | <a href="#">FL FIELDWIRING EN</a><br><a href="#">PI PROFINET CABLING EN</a>            |
| Product Change Notification                 | <a href="#">PCN-PB47-20180213-00-A_EN</a><br><a href="#">PCN-PB47-20180213-00-A_DE</a> |
| User Documentation                          | <a href="#">MAN IE GUIDE DE</a><br><a href="#">MAN IE GUIDE EN</a>                     |

## Industrial Ethernet IE-C6FP8LD0035M40M40-D

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Wiring

|      |   |                |   |      |
|------|---|----------------|---|------|
| RJ45 | 1 | white (orange) | 1 | RJ45 |
|      | 2 | orange         | 2 |      |
|      | 3 | white (green)  | 3 |      |
|      | 4 | blue           | 4 |      |
|      | 5 | white (blue)   | 5 |      |
|      | 6 | green          | 6 |      |
|      | 7 | white (brown)  | 7 |      |
|      | 8 | brown          | 8 |      |

## Dimensioned drawing

