

**Industrial Ethernet  
IE-C5ES8UG0003M40M40-G**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Industrial Ethernet connection technology by Weidmüller offers the optimal solution for the infrastructure of your machine, system or factory. All connection technology is available from one source.

The benefits for you:

- IEC-standardised connectors, in the variants 1, 4, 5, 6 and 14
- Cat. 6 throughout<sub>A</sub> with **STEADYTEC**® technology
- pre-assembled cables and cables sold by the metre
- Copper and fibre-optic cables
- in IP20 and IP67
- all relevant industrial connections: RJ45, M12, SC, ...
- comprehensive range of accessories

**General ordering data**

Type	IE-C5ES8UG0003M40M40-G
Order No.	<a href="#">116600003</a>
Version	System cable, RJ45 IP 20, RJ45 IP 20, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PUR, 0.3 m
GTIN (EAN)	4050118200508
Qty.	1 pc(s).

**Industrial Ethernet  
IE-C5ES8UG0003M40M40-G**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**
**Dimensions and weights**

Length	0.3 m	Length (inches)	0.012 inch
Net weight	30 g	Insulation cross-section	1 mm

**Temperatures**

Operating temperature, max.	80 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	80 °C	Storage temperature, min.	-40 °C
Operating temperature	-40 °C...80 °C	Storage temperature	-40 °C...80 °C
Installation temperature	-10 °C...60 °C		

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Standards**

Corrosiveness of fumes	to IEC 60754-2	Generic communication cable facilities	ISO / IEC 11801:2002, EN 50173-1:2007
Standard, assembly	UL-Style 20963 (80°C/30V)		

**Cable structure**

Wire material	Stranded tin-plated copper wire	Standard designations	SF/UTP, IE-7IC4x2xAWG23/1-PUR 02YSC 11Y PIMF
Strands	7	Cross-section	4*2*AWG 26/7 - 4*2*0.128 mm <sup>2</sup>
Insulation	PE	Insulation cross-section	1 mm
No. of wires	8	Arrangement of wire cores	Twisted pair
Colour sequence or wires - wire pairs	white - blue, white - orange, white - green, white - brown	Shielding	SF/UTP
Complete shielding	Aluminium foil, Shielding braid made from copper wiring	Shielding braid thickness	0.1 mm
Material sheath	PUR	Sheath diameter, min.	5.7 mm
Sheath diameter, max.	6.1 mm	Sheathing colour	green (RAL 6018)

**Electrical properties of cable**

Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)	Test voltage: wire-wire-shield	700 V AC
Characteristic impedance	100 ± 5 Ω at 100MHz	Loop resistance	290 Ω/km
Deviation	25 ns/100m	Capacity at 1 kHz	50 nF/km
Signal propagation time	4.85 ns/m		

## Industrial Ethernet IE-C5ES8UG0003M40M40-G

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

# Technical data

### Mechanical and material properties of cable

Min. bending radius, once only	5 x cable diameter	Min. bending radius, repetitive	10 x cable diameter
Abrasion resistance	very good	Resistance to spread of flame	in accordance with IEC 60332-1
Resistance to oils	in accordance with IEC 60811-2-1	UV-resistant	Yes
Silicone-free	Yes	Halogen	halogen-free, according to IEC 60754-2
Corrosiveness of fumes	to IEC 60754-2		

### plug

Connector left	RJ45 IP 20	Connector right	RJ45 IP 20
----------------	------------	-----------------	------------

### Classifications

ETIM 3.0	EC001262	ETIM 5.0	EC000748
ETIM 6.0	EC002599	UNSPSC	26-12-16-06
eClass 5.1	27-06-18-02	eClass 6.2	27-06-03-90
eClass 7.1	27-06-03-90	eClass 8.1	27-06-03-90
eClass 9.0	27-06-03-08	eClass 9.1	27-06-03-08

### Approvals

ROHS	Conform
------	---------

### Downloads

Brochure/Catalogue	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a>
Product Change Notification	<a href="#">PCN-PB47-20180213-00-A_EN</a> <a href="#">PCN-PB47-20180213-00-A_DE</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>