

NEOZED, fuse base, D02, 1-pole, 63 A, Un AC: 400 V, Un DC: 250 V



Model	
Product brand name	NEOZED
Product designation	Fuse base
Design of the product	NEOZED fuse base installation
version	with protection against contact BGV A3
General technical data	
Number of poles	1
Size of fuse system / acc. to DIN EN 60269-1	D02
Supply voltage	
Operating voltage / rated value	400 V
Dissipation	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	1 W
Main circuit	
Operating current / rated value	63 A
Product details	
Product component / Cover	Yes

Mechanical Design

Height	83 mm
Width	27 mm
Depth	64 mm
Mounting type	DIN rail
Net weight	116 g
Material / of D fuse base	plastic

Certificates

Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F
F

General Product Approval

Declaration of Conformity

Test Certificates



VDE



EG-Konf.

[Type Test Certificates/Test Report](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SG1701>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SG1701>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG1701

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



