

Valve connectors - SAC-5P-MR/AD-2L SCO - 1458606

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Valve connectors, 5-position, Plug angled M12 SPEEDCON, A-coded, on Valve connector AD (pressure switch), with 2 LEDs



Key commercial data

package_quantity	1
GTIN	4046356639057

Technical data

Dimensions

Central screw valve connector	M3 x 29
-------------------------------	---------

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C (valve plug)
Degree of protection	IP65
	IP67

General

Rated current at 40°C	4 A
Rated voltage	24 V AC
	24 V DC
Number of positions	5
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Standards/regulations	M12 connector IEC 61076-2-101
	Valve connector EN 175301-803
Status display	2 LEDs
Overvoltage category	II
Degree of pollution	3
Connection method	M12 connector
Insertion/withdrawal cycles	50 (Valve connector)
	≥ 100 (M12 connector)
Torque	0.6 Nm (Valve connector)

Valve connectors - SAC-5P-MR/AD-2L SCO - 1458606

Technical data

Material

Flammability rating according to UL 94	HB
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	PA66
Valve plug contact material	CuSn
Valve plug contact surface material	Sn
Valve plug contact insert material	PA 6.6
Material housing valve plug	TPU
Material, knurls	Zinc die-cast, nickel-plated
Sealing material	TPU (Seal molded)

Standards and Regulations

Standard designation	M12 connector
Standards/regulations	IEC 61076-2-101
Standard designation	Valve connector
Standards/regulations	EN 175301-803
Flammability rating according to UL 94	HB

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27143423
eCl@ss 5.1	27143400
eCl@ss 6.0	27279200
eCl@ss 7.0	27440104
eCl@ss 8.0	27440104
eCl@ss 9.0	27440105

ETIM

ETIM 4.0	EC002062
ETIM 5.0	EC002062
ETIM 6.0	EC002925
ETIM 7.0	EC002925

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501

Valve connectors - SAC-5P-MR/AD-2L SCO - 1458606

Classifications

UNSPSC

UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

Approvals

DNV GL / CSAus / EAC /

Approval details

DNV GL #

CSAus	
Nominal voltage UN	24 V
Nominal current IN	4 A
mm ² /AWG/kcmil	

EAC

Accessories

Torque tool

TSD-M 1,2NM - 1212224



Screwdriver tools


SF-BIT-PH 1-70 - 1212582




Drawings

Valve connectors - SAC-5P-MR/AD-2L SCO - 1458606

Dimensional drawing




Circuit diagram



Contact assignment of M12 plug and valve connector


Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side

Valve connectors - SAC-5P-MR/AD-2L SCO - 1458606

Schematic diagram



Valve plug connector pin assignment, type AD

Phoenix Contact 2019 © - all rights reserved
<http://www.phoenixcontact.com>