Constant Voltage LED Power Supply

SLT30-12VFC-UN SLT30-24VFC-UN



Product description:

This LED power input voltage of 120-240VAC, the output constant voltage 12V or 24V, for load parallel voltage LED. This LED power supply shape slim and thin. LED power supply has open circuit, short circuit, overload or over temperature protection function, troubleshooting, the power will automatically restart.





Standards:

EN61347-1

EN61347-2-13

EN61547

EN55015

EN61000-3-2

EN61000-3-3

EN62384

EN62493

UL8750

UL1310

FCC15B

Characteristics:

- The standard requirements to meet EN60335-2-89;
- Power section is divided into 30W,75W and output voltage have 12V and 24V;
- Surge level, according to EN61000-4-5 :level 4 L, N: 2000V, L, N-PE: 4000V
- Metal case for indoor or outdoor installation
- Suitable for class I luminaire
- Suitable for dry/damp/wet locations
- Class 2 power unit
- Life to meet the 5-year warranty requirements, failure rate to meet 0.1% / 1000h



Specifications:


Model		SLT30-12VFC-UN	SLT30-24VFC-UN	
Output	turn on time(S)	≤0.5	≤0.5	
	output power(W)	30	30	
	output votage(V)	12	24	
	output voltage tolerance	+/-5%	+/-5%	
	ripple voltage(mV)	90(Vp-p)	100(Vp-p)	
	working current range(A)	0-2.5	0-1.25	
	dimming interface	No		
	dimming range	n/a		
Input	rated supply voltage(Vac)	120-240	120-240	
	voltage range(Vac)	108-264	108-264	
	line frequency(Hz)	50/60	50/60	
	input current(mA)	350	350	
	efficiency 2	83.5%	84.5%	
	average efficiency 6	79.5%	80.0%	
	no load power consumption(W)	≤0.5	≤0.5	
	power factor ²	0.95	0.95	
	inrush current(lpk)	18A/180us	18A/180us	
Protection	over voltage protection	YES		
	short circuit protection	YES		
	over temperature protection	YES		
	automatic restart	YES		
	over load protection	YES		
	surge capacity	L-N: 2KV L,N-PE: 4KV		
Ambient and Life	Ta(℃)	-2050	-2050	
	Tc max.(℃)	75	75	
	Storage Temperature(°C)	-3080		
	ambient humidity range	5%85%RH, Not condensing		
	nominal life-time(hrs)	50'000@Tc=75 C		
	guarantee(years)	5		
	MTBF(hrs)	100'0000		
	audible noise(dB)	<25dBA		
Other -	weight(g)	200		
	dimensions (L×W×H)(mm)	275x30x16.5		
	casing material	Aluminum		
	housing colour	Silver		
	type of protection	IP67		
	protection class	Class I		
Note	Tested at full load,230Vac.Ref Calculate the model's average rated current and then computing the second	olerance, line regulation and load regulation. Refer to "Power Factor" and "EFFICIENT" curve graphs. rage efficiency for each test voltage by testing at 100%, 75%, 50%, and 25% of outing the simple arithmetic erage of these four values. Illy mentioned are measured at nominal voltage input, rated load and 25 of or ered as a component that will be operated in combination with final equipment. The peed of the complete installation, the final equipment manufacturers must be complete installation again."		



Dimensions: mm




Wiring diagram:







Electrical curves:









note
For constant current power supply, "LOAD" means the percentage of the maximum rated output voltage.
For constant voltage power supply, "LOAD" means the percentage of the maximum rated output current.

Last update:13 Sep, 2018

Page: 4 of 5



Sales & Technical Support:

Self Electronics Co.,Ltd.

Add: No. 1345 Ju Xian Road, Ningbo Hi Tech Park, Ningbo,

Tel: 0086-574-28805765,28805658 (For English Assistance) 0086-574-28805678 (For Chinese Assistance)

Fax: 0086-574-28805656 E-mail: sales@self-ecg.com http://www.self-ecg.com

SELF ELECTRONICS GERMANY GMBH

Add:August-Horch-Str. 7,51149 Koeln Tel: 0049 2203 18501-0 Fax: 0049 2203 18501-199

E-mail: saleseu@self-electronics.com

Self Electronics Co., Ltd., Shenzhen Office

Add: Room2007, Xinglang Xuan, Xinghe Mingju, Fuming Road, Futian District, Shenzhen
Tel: 0086-755-83558850, 83558851
Fax: 0086-755-83558840



^{*}Due to continuous improvements and innovations, specifications are subjected to change without notice.