

Industrial Ethernet IE-SW-BL05T-1GS-4GTPOE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Product image



- 4 x IEEE 802.3af/at compliant PoE ports
- 12/24/48 VDC redundant wide-range power supply
- Integrated DC/DC converter for supplying 48 V PoE devices over the entire input voltage range from 12 to 57 VDC
- Intelligent power consumption detection and classification
- Variations with copper and fibre-optic interface (multimode and singlemode)

General ordering data

Type	IE-SW-BL05T-1GS-4GTPOE
Order No.	1504380000
Version	Network switch, unmanaged PoE, Gigabit Ethernet, Number of ports: 4 * RJ45 10/100/1000BaseT(X) PoE+, 1* Slot 1000BaseSFP, IP30, -40 °C...75 °C
GTIN (EAN)	4050118312430
Qty.	1 pc(s).

**Industrial Ethernet
IE-SW-BL05T-1GS-4GTPOE**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	29 mm	Width (inches)	1.142 inch
Height	135 mm	Height (inches)	5.315 inch
Depth	105 mm	Depth (inches)	4.134 inch
Net weight	360 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

EMC conformity and approvals

EMC standards	FCC Part 15 Subpart B Class A, EN 55022 Class A, EN 61000-4-2 (ESD), Stage 3, EN 61000-4-3 (RS), Stage 3, EN 61000-4-4 (EFT), level 4, EN 61000-4-5 (surge), level 4, EN 61000-4-6 (CS), Stage 3, EN 61000-4-8	Security	UL508
Shock	according to IEC 60068-2-27	Vibration	according to IEC 60068-2-6

Environmental conditions

Humidity	5...95 %, no condensation	Operating temperature, max.	75 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Interfaces

DIP switch	Broadcast storm protection enable/disable	LED indicator	PWR1, PWR2, 10/100/1000M (TP-Port), 100/1000M (SFP-Port), PoE
Note 1	When connecting a single-mode fiber transceiver over a short distance, we recommend using an attenuator to prevent the transceiver from being damaged by excessive optical power.	Note 2	The SFP slot can only be used with Weidmüller SFP transceivers. Third-party SFP transceivers are not accepted by the switch.
Number of ports	4 * RJ45 10/100/1000BaseT(X) PoE+, 1* Slot 1000BaseSFP	PoE pin assignment	V+, V+, V-, V-, for pins 1, 2, 3, 6 (endspan, MDI alternative A)
RJ45 ports	10/100/1000BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port		

MTBF

MTBF	1,257,910 hrs	MTBF	Telcordia (Bellcore), GB
------	---------------	------	--------------------------

Data sheet

**Industrial Ethernet
IE-SW-BL05T-1GS-4GTPOE**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Power supply

Connection type	2 removable 2-pole terminal blocks	Current consumption	6.83 A with 24 V DC (at full PoE+ load), 3.28 A with 48 V DC (at full PoE+ load)
Reverse polarity protection	Available	Supply voltage, max	57 V DC
Supply voltage, min.	20 V DC	Voltage supply	24/48 V DC, 2 redundant inputs

Switch characteristics

Jumbo frame support	up to 9.6 KB	MAC table size	8 K
Packet buffer size	1,024 Kbit		

Technical data

Housing main material	Aluminium	Protection degree	IP30
Type of mounting	Rail, Panel (with optional mounting kit)		

Technology

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control, Back pressure flow control
Standard	IEEE 802.3af for Power-over-Ethernet, IEEE 802.3at for Power-over-Ethernet, IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X), IEEE 802.3ab for 1000BaseT(X), IEEE 802.3z for 1000BaseX, IEEE 802.3x for flow control		

Classifications

ETIM 5.0	EC000734	ETIM 6.0	EC000734
eClass 6.2	19-17-01-06	eClass 7.1	19-17-01-06
eClass 8.1	19-17-01-06	eClass 9.0	19-17-01-06
eClass 9.1	19-17-01-06		

Approvals

Approvals



ROHS Conform

Data sheet**Industrial Ethernet
IE-SW-BL05T-1GS-4GTPOE**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Downloads**

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
Brochure/Catalogue	CAT 9 IETH 15/16 EN
Engineering Data	STEP
Product Change Notification	Product Change Notification IE-SW-BL05-4GTPoE-series
User Documentation	Hardware Installation Guide