



# USB Type-C™ Multiport Travel Dock, 6-Port



## Quick Installation Guide

DA-70867

### 1.0 INTRODUCTION

This is a USB-C to two USB 3.0, HDMI, Micro SD, SD/MMC, Type-C™ Data and PD Charging Adapter. The USB 3.0 port allows you to connect USB device or another hub to the host USB-C computer, the USB-C female port supports both PD Charging and data; the HDMI port allows you to enjoy high definition picture or video on big screen, and the Micro SD and SD/MMC port allows you to read information in the memory card on the host PC. It can work on all PCs and mobile phones which support DP Alt-mode.

## 2.0 FEATURES

- **Interface:**
  1. Type-C™ Female x1 (connect to Type-C™ host PC with our equipped Type-C™ M to M cable)
  2. Type-C™ Female x1 (for data and PD Charging)
  3. USB-A Female x2
  4. HDMI Female x1
  5. SD slot x1, Micro SD slot x1
- Support USB 3.0 super speed (5Gbps) transmission, downward compatible with USB 2.0
- One of the USB-A port can be up to 7.5W (5V/1.5A)
- USB 3.0 port supports to charge and transmit data for the USB device simultaneously
- Support HDMI resolution up to 4Kx2K@30Hz
- Type-C™ female port supports both data (5Gbps) and PD Charging 100W (20V/5A)
- Multiple USB-C interfaces support plug and play, hot swap
- Support Secure Digital v3.0 UHS-I (Ultra High Speed):  
SDR12(12.5Mbyte/s)/SDR25(25Mbyte/s)/SDR50(50Mbyte/s)/DDR50(50Mbyte/s)/SDR104(104Mbyte/s)
- Note: Support two card slots to work simultaneously
- Support Fast Role Swap of PD 3.0, the connected device will not get disconnected while plugging in and out PD Adapter
- Easy to use and carry
- Note: Description of the Detached Type-C™ M to M Cable
- It is a USB 3.1 Type-C™ Gen2 Full-featured cable with speed up to 10Gbps; E-marked IC and power output up to 5Amp
- This product only functions well with our equipped Type-C™ M to M cable or cable produced by us that has the same spec with the original one. So to guarantee the proper functioning of this product, if the equipped cable is lost by accident, please contact our sales to buy another cable of the same spec and avoid using cable produced by other manufacturers.

### 3.0 SPECIFICATIONS

<b>Input/Output Connector</b>	
Input	USB-C Female x1 (with our Type-C™ M to M cable)
Output	USB 3.0 Female x2 USB-C Female x1 (for data and Charging) HDMI Female x1 Micro SDX1 SD/MMCX1
<b>Environmental</b>	
Operating Temperature	0°C to +45°C
Operating Humidity	10% to 85% RH (no condensation)
Storage Temperature	-10°C to +70°C
Storage Humidity	5% to 90% RH (no condensation)
<b>Power Supply</b>	
USB-C Female Port	Up to 100W (20V/5A)

### 4.0 PACKAGE CONTENTS

Before attempting to use this unit, please check the packaging and make sure the following items are contained in the shipping carton:

- Main unit x1
- User Manual x1

## 5.0 OPERATION

- 1) Connect the USB-C Female port of this product to USB-C device.
- 2) Connect the two USB 3.0 outputs of this product to two USB 3.0/2.0 devices
- 3) Connect HDMI output of this product to HDTV with one HDMI cable
- 4) Insert Micro SD, SD/MMC card into the responding slots
- 5) Connect the USB-C charging port, it can charge for the host computer and support power for this product simultaneously

### Note:

- 1) Not all USB-C ports support all features of the USB Type-C™ standard. Make sure your notebook's USB-C port supports DisplayPort Alternate Mode (DP-Alt Modi) and USB Power Delivery (PD).
- 2) The video output capability depends on the graphic card of your notebook and the connected monitor.



## 6.0 CONNECTION DIAGRAM



Hereby Assmann Electronic GmbH, declares that the Declaration of Conformity is part of the shipping content. If the Declaration of Conformity is missing, you can request it by post under the below mentioned manufacturer address.

[www.assmann.com](http://www.assmann.com)

Assmann Electronic GmbH  
Auf dem Schüffel 3  
58513 Lüdenscheid  
Germany

