


Description	: Lithium Battery
Chemical System	: Lithium Manganese Dioxide
Nominal Voltage	: 3.0 Volts
Nominal Capacity	: 800mAh @ 10mA to 1.8V at 23°C
Dimensions	: Ø15.3 mm x 26.5 mm
Terminals	: Flat
Jacket	: PVC Resin Label
Shelf Life	: Up to 10 years
Average Weight	: App. 10g
Max. Constant Current	: 1000mA
Max. Pulse Current	: 2500mA
Application	: Smoke Detector, Sensors, Home Security Products
Operating Temperature	: -40°C to +60°C
UL Standard	: UL1642 (File no. MH46184) UL2054 (File no. MH25972)
IEC Standard	: IEC60086-4
UN Standard	: UN38.3

Cross References:

JIS	GP	Panasonic	Energizer	Duracell
CR15H270	CR2	CR-2	EL1CR2	DLCR2

Model No.: **GPCR2**


Ultra+




Label Area

Unit : mm

Discharge Characteristics
900mA, 3 seconds on / 27 seconds off



Continuous Discharge at 23°C



The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.

www.gpbatteries.com

Manufacturer reserves the right to alter or amend the design, model and specification without prior notice.
Copyright© GPI International Ltd. - All rights reserved

Member
Gold Peak Group

04/2020