



MOUNTING INFORMATION & WIRING DIAGRAMS

732 Series - (Direct Current) : 10-80 VDC




Round Bezel 3 Hole Mount :
Panel Cutout 2.00 (50.8) diameter opening.
Three 0.149 (3.8) holes equally spaced on 2.52 (64.26) bolt circle diameter.

Max. Panel Thickness : 0.401 (10.20)




Rectangular Mount :
Panel Cutout 1.45 x 0.95 (36.8 x 24.1) Rectangular opening.

Max. Panel Thickness : 0.401 (10.20)



Round Bezel Mount :
Panel Cutout 2.00 (50.8) diameter opening.


Max. Panel Thickness : 0.401 (10.20)



Rectangular 2 Hole Mount :
Panel Cutout 1.45 x 0.95 (36.8 x 24.1) Rectangular opening. Two .150 (3.8) holes spaced 1.750 (44.5).


Max. Panel Thickness : 0.401 (10.20)

All dimensions are in Inches , () dimensions are in mm




Cup Mount :
Panel Cutout 2.00 (50.8) diameter opening

Max. Panel Thickness : 0.401 (10.20)



Stirrup Mount :
Panel Cutout 2.00 (50.8) diameter opening


Max. Panel Thickness : 0.401 (10.20)



Square Housing 48 x 48 Panel cutout 45 x 45 opening.

Max. Panel Thickness : 0.401 (10.20)

732 Series Wiring Diagram (Polarity Sensitive) For DC Hour Meter Application



See Over Leaf For Panel Cutout Details.