

RCBO compact 1P+N 6 kA type A 30 mA C16



Model	
Product brand name	SENTRON
Product designation	RCBO
Design of the product	Instantaneous
General technical data	
Number of poles	2
Number of poles / Note	1P+N
Number of poles / with protection	1
Tripping characteristic class	C
circuit-breaker / Design	5SV1
Mechanical service life (switching cycles) / typical	10 000
Overvoltage category	III
Voltage	
Surge current resistance / at (8/20) $\mu$ s	1 kA
Supply voltage	
Type of voltage	AC
Current / at AC / rated value	16 A
Supply voltage	

• for testing equipment / minimum	195 V
Supply voltage frequency / rated value	50 Hz
<b>Protection class</b>	
Protection class IP	IP20, if the distribution board is installed, with connected conductors
<b>Switching capacity</b>	
Breaking capacity short-circuit current (I <sub>cn</sub> ) / according to EN 61009-1 / rated value	6 kA
Switching capacity current	
• acc. to EN 60898 / rated value	6 kA
• acc. to IEC 60947-2 / rated value	10 kA
Rated residual switching capacity (I <sub>Δm</sub> ) / according to IEC 61009-1	4.5 kA
Energy limiting class	3
<b>Dissipation</b>	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	1.7 W
<b>Current</b>	
Tripping residual current / rated value	30 mA
Tripping residual / rated value / derated current	
• at 30 Cel	16 A
• at 40 Cel	15.2 A
• at 45 Cel	14.72 A
• at 50 Cel	14.24 A
• at 55 Cel	13.76 A
• at 60 Cel	13.28 A
• at 65 Cel	12.8 A
• at 70 Cel	12.32 A
Type of fault current	A
<b>Product details</b>	
Product function / neutral conductor switching	Yes
Product feature / Touch protection	Yes
Product feature	
• halogen-free	Yes
• silicon-free	Yes
<b>Connections</b>	
• Connectable conductor cross-section	
— solid	0.75 ... 16 mm <sup>2</sup>
— stranded	0.75 ... 16 mm <sup>2</sup>
• Connectable conductor cross-section / finely stranded / with core end processing	0.75 ... 10 mm <sup>2</sup>

Tightening torque / with screw-type terminals	1.2 ... 2 N·m
Position / of power supply cord	Either top or bottom

### Mechanical Design

Height	90 mm
Width	18 mm
Depth	77 mm
Installation depth	70 mm
Number of width units	1
Mounting position	any
Net weight	117 g

### Environmental conditions

Influence of the surrounding temperature	Max. 95% humidity
Ambient temperature	-25 ... +45 °C
• during storage	-40 ... +75 °C

### Certificates

Reference code	
• acc. to DIN EN 61346-2	F
• acc. to DIN EN 81346-2	F

<b>Declaration of Conformity</b>	<b>Test Certificates</b>	<b>other</b>
----------------------------------	--------------------------	--------------

[Special Test Certificate](#)

[Miscellaneous](#)



EG-Konf.

### Further information

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

#### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SV1316-7KK16>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SV1316-7KK16>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SV1316-7KK16](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SV1316-7KK16)

#### CAX-Online-Generator

<http://www.siemens.com/cax>

#### Tender specifications

<http://www.siemens.com/specifications>







