

Features:

- self-priming, multi-stage centrifugal pump with low-noise operation
- suction head up to 8,5 m
- electronic pressure switch for automatic switch-on / -off
- dry-run protection
- thermal overload protection
- stainless steel pump housing and screws
- aluminium motor housing (MP350 stainless steel)
- impellers and guide wheels made of wear-resistant plastic; motor shaft made of stainless steel
- sealed with mechanical seal
- suction connection 1" FPT; pressure connection 1 1/4" MPT

Application:

- irrigation of home and garden
- water supply

Scope of delivery:

- pre-assembled ready for connection with 1,5 m power cable
- electronically adjustable pressure switch with dry-run protection




Product benefits:

- durable and reliable
- automatic operation and dry-run protection
- integrated thermal winding protection to prevent overheating damage

Technical data:

Art.no.	U [V]	P ₁ [W]	P ₂ [W]	I _n [A]	n [min ⁻¹]	Q _{max} [m ³ /h]	H _{max} [m]	P ₀	L [mm]	H [mm]	Weight [kg]
21302	230	1.000	700	4,4	2800	4,3	44,0	G1	401	354	11,1

Characteristics:



Materials:

Material impeller:	PPO GF20
Seal pump:	mechanical seal
Material pump housing:	stainless steel AISI 304

Dimensions:

