

**Industrial Ethernet
IE-ANT-O-AH-360-5-NF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Product image

- For usage with the Weidmüller WLAN Access Point
- Omni-directional and planar antennas
- For use in the 2.4 GHz and 5 GHz band
- Open-air use possible thanks to the robust design (up to IP68)
- Cable for connecting external antennas to the Weidmüller WLAN Access Point in 2-metre and 4-metre versions

General ordering data

Type	IE-ANT-O-AH-360-5-NF
Order No.	1367120000
Version	Omni-directional antenna, 5 GHz band, Gain of 5 dBi, Vertical, 1x N-type female, bottom, IP64, Impedance: 50 Ω
GTIN (EAN)	4050118186345
Qty.	1 pc(s).

Industrial Ethernet IE-ANT-O-AH-360-5-NF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Height	160 mm	Height (inches)	6.299 inch
Weight	300 g	Net weight	210 g
Diameter	16 mm		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Enclosure material

Housing main material	PP
-----------------------	----

Included in delivery

Included in delivery	1 x antenna, 1 x mounting bracket, 2 x clamps for mast assembly
----------------------	---

Technical data

3dB beamwidth (horizontal)	360°	3dB beamwidth (vertical)	25°
Antenna gain	5 dBi	Composite power max.	6 W
Frequency range	5150 - 5875 (Mhz)	Impedance	50 Ω
Polarisation	Vertical	Radiation	Omnidirectional
Standing wave ratio	< 1.7	Type of connection	1x N-type female, bottom
Vertical electrical tilt	0°		

Environmental conditions

Applications	for indoor and outdoor use	Operating temperature, max.	75 °C
Operating temperature, min.	-45 °C	Storage temperature, max.	75 °C
Storage temperature, min.	-45 °C	Wind load	Frontal, Lateral, 7 N, @ 160 Km/h

Classifications

ETIM 6.0	EC001698	eClass 6.2	27-25-92-90
eClass 7.1	27-25-92-90	eClass 8.1	19-17-01-90
eClass 9.0	19-07-01-05	eClass 9.1	19-07-01-05

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 9 IETH 15/16 EN
--------------------	-------------------------------------