

Industrial Ethernet IE-SR-2GT-LTE/4G-US

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Product image



High performance industrial-security router

- Variations with 2 or 6 Gigabit ports
- NAT masquerading, 1:1 network mapping and port forwarding
- VPN function (u-link Remote Access Service, OpenVPN and IPsec)
- Key switch function to control a WAN/VPN connection
- 6-port variations with expanded routing functionality
- Variations with integrated 4G/LTE modem for high-speed, internet-based mobile communications access
- Cost-efficient variation without VPN functionality for NAT and security applications (1489940000, IE-SR-2GT-LAN-FN)
- Variations with DNV-GL approval for use in a maritime environment

General ordering data

Type	IE-SR-2GT-LTE/4G-US
Order No.	2535780000
Version	Security/NAT/VPN/U-link Router, with integrated LTE / 4G modem, US model, Gigabit Ethernet, 2 * RJ45 10/100/1000BaseT(X), IP20, -20 °C... 70 °C
GTIN (EAN)	4050118547597
Qty.	1 pc(s).

**Industrial Ethernet
IE-SR-2GT-LTE/4G-US**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Dimensions and weights**

Width	35 mm	Width (inches)	1.378 inch
Height	170 mm	Height (inches)	6.693 inch
Depth	140 mm	Depth (inches)	5.512 inch
Net weight	700 g		

Industrial Ethernet IE-SR-2GT-LTE/4G-US

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

4G/LTE - specification

Frequency band	Americas: LTE: Band 2 (1900 MHz), Band 4 (AWS) (1700/2100 MHz), Band 5 (850 MHz), Band 13 (700 MHz), Band 17 (700 MHz), Band 25 (1900 MHz G Block); CDMA EVDO Release 0 y EVDO Release A: BC0 (Cellular 800 MHz), BC1 (PCS 1900 MHz), BC10 (Secondary 800 MHz); UMTS: band 1 (2100 MHz); band 2 (1900 MHz); band 4 (AWS 1700/2100 MHz); band 5 (850 MHz); band 8 (900 MHz); GSM/GPRS/EDGE: Quad-Band (850/900/1800/1900 MHz)	Mode of operation	Permanent connection, Manual connection control via web interface, Fallback connection with active ICMP monitoring of the target IP via Ethernet
Standard	LTE: 3GPP Release 9, UMTS: 3GPP Releases 5, 6, 7, 8, GSM/GPRS/EDGE: 3GPP Release 99, GERAN Feature Package #1, CDMA (Americas): TIA/EIA/IS-2000.1 through .6. cdma2000® Standards for Spread Spectrum Systems. Release 0. April 2000; TIA/EIA/IS-2000.1-1 through .6-1. cdma2000® Addendum 1 April 2000; TIA/EIA/IS-2000.1-2 through .6-2. cdma2000® Addendum 2 June 2001; TIA/EIA/IS-95-B. Mobile Station-Base Station Compatibility Standard for Dual-Mode Spread Spectrum Systems. December 4, 1998; TIA/EIA/IS-. cdma2000® High Rate Packet Data Air Interface Specification. Nov. 2000	Transmission rate	Max. download rate: 100 Mbps, Max. upload rate: 50 Mbps
Transmit power	LTE Bands 1, 2, 3, 4, 5, 8, 13, 17, 20, 25: +23 dBm ± 1 dB; LTE Band 7: +22 dBm ± 1 dB, UMTS Bands 1, 2, 4, 5, 8 : +23 dBm ± 1 dB, GSM850 CS and EGSM900 CS: +32 dBm ± 1 dB (mode GMSK) +27 dBm ± 1 dB (mode 8PSK), DCS1800 CS and PCS1900 CS: +29 dBm ± 1 dB (mode GMSK) +26 dBm ± 1 dB (mode 8PSK), CDMA: Band Class 0 (Cellular) +24 dBm +0.5/-1 dB; Band Class 1 (PCS) +24 dBm +0.5/-1 dB; Band Class 10 (Cellular) +24 dBm +0.5/-1 dB	Wireless module	LTE / HSPA+ multiband wireless module (4G / 3G / 2G) for fast wireless Internet access

Creation date May 27, 2019 3:49:18 PM CEST

Industrial Ethernet IE-SR-2GT-LTE/4G-US

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Network Services/Firewall/Management

Firewall	IPv4 Stateful Packet Inspection Firewall (incoming/outgoing), NAT masquerading, 1:1 NAT, Port forwarding, layer 2/3 filter (VLAN ID, VLAN QoS Tag, MAC address, EtherType frame), Auto-learning function to create packet filter rules (analysis of network traffic), Layer 2/3-based packet prioritisation (Ethernet Frame, IP Header, VLAN Tag)	Management	Configuration via WEB interface (HHTP/HTTPS), Language interface can be switched to German or English, Configuration support through detailed help information (tool tip), Configurable multi-user access with freely definable rights, Support for SNMP v1/v2/v3, event log/syslog
Network services	DHCP Server / DHCP Relay, DNS relay, NTP client, DynDNS (DHCP client acc. to RFC 2136)		

VPN

IPsec	Configurable as IPsec server or client, Authentication via PSK (userid, password) or X.509 certificates, Hardware-based encryption for faster data throughput, Maximum 64 simultaneous connections (sub-network to sub-network or as IPsec server), Encryption algorithms DES-56, 3DES-168, AES-128, AES-192, AES-256	OpenVPN	Configurable as OpenVPN server or client (Layer 2 and Layer 3), Authentication via X.509 certificate, Tunnel support via HTTP proxy, Maximum 10 different client or server configurations, Unlimited number of client connections in server mode
u-link	OpenVPN-based remote access service via the Weidmüller u-link cloud		

Miscellaneous

Diagnostics	Remote capture function for network diagnostics via a connected PC (Wireshark)	Modbus/TCP	Integrated Modbus-TCP server for status queries and software-based enabling/disabling of VPN connections
Monitoring	Client monitoring (per ICMP) with alarm function in the event of a fault		

Modes of operation

IP router	IP routing (IPv4, Layer-3) with SPI firewall (Stateful Packet Inspection)	Transparent bridge	2-port switch with additional layer-2 filter
-----------	---	--------------------	--

**Industrial Ethernet
IE-SR-2GT-LTE/4G-US**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**EMC conformity and approvals**

EMC standards	FCC Part 15, Class A, EN 61000-6-4, EN 61000-6-2	Shock	according to IEC 60068-2-27
Vibration	according to IEC 60068-2-6		

Environmental conditions

Humidity	5 - 90 %, no condensation	Operating temperature, max.	70 °C
Operating temperature, min.	-20 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-20 °C		

Guarantee

Time interval	3 years
---------------	---------

Interfaces

Connector for external antennas	SMA (socket)	Digital inputs	Cut: physically disconnects (Link Down) the WAN port (24 V in), VPN-initiate: establishes a pre-configured VPN connection (24 V in)
Digital outputs	Alarm: indicates a configurable network state or fault (24 V out), VPN-active: indicates an active VPN connection (24 V out)	LED indicator	Indication of voltage status, Status, Section, Alarm, Active VPN connection, Mobile phone connection
Number of ports	2 * RJ45 10/100/1000BaseT(X)	RJ45 ports	10/100/1000BaseT(X), auto negotiation, Full-/half-duplex mode
Reset button	Restoration of factory settings	USB port	USB 2.0 interface for firmware update or restoration of the device configuration via USB flash drive

Power supply

Current consumption	max. 0.6 A at 24 V DC	Voltage supply	1x 24 V DC (7 to 36 V DC), NEC class 2, (for use in conformity with UL specifications: 7 - 30 V DC)
---------------------	-----------------------	----------------	---

Technical data

Housing main material	diecast aluminium	Protection degree	IP20
Type of mounting	Rail, VESA 75		

Classifications

ETIM 6.0	EC001478	eClass 6.2	19-17-01-03
eClass 9.0	19-17-01-03	eClass 9.1	19-17-01-03

Data sheet

**Industrial Ethernet
IE-SR-2GT-LTE/4G-US**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
Engineering Data	STEP
Product Change Notification	Firmware Release Notes
Software	SNMP MIB file u-link VPN-Client - Version 2.0.129 Router Search Utility Firmware - Version 3.2.3
User Documentation	Hardware Installation Guide Manual u-link Technical User Guide User Note - Secure Router Configuration