

**Industrial Ethernet
IE-MCT-1RS232/485-1ST**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Serial/fibre-optic converter**

Media converter for implementing serial, copper-based interfaces on fibre-optic cables and vice versa. Facilitates communication between terminal devices with type RS232/422/485 serial interface over a distance of up to 5 km.

- Ring and point-to-point transmission modes
- Extension of the RS232/422/485 transmission to up to 5 km
- Supports baud rates of 50 bps to 921.6 Kbps
- Expanded temperature range of -40 to 75°C
- Compact design

General ordering data

Type	IE-MCT-1RS232/485-1ST
Order No.	1362950000
Version	Serial/fibre-optic converter, 1 x terminal block for RS232/422/485, 1 x ST multimode, IP30, -40 °C...75 °C
GTIN (EAN)	4050118165203
Qty.	1 pc(s).

Industrial Ethernet IE-MCT-1RS232/485-1ST

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	90.2 mm	Width (inches)	3.551 inch
Height	100 mm	Height (inches)	3.937 inch
Depth	22 mm	Depth (inches)	0.866 inch
Net weight	130 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Serial interface

Baud rate	50 bit/s to 921.6 kbit/s	Connection type	1 removable 3-pole terminal block
Interface standards	RS-232/422/485	RS-485 data direction control	ADDC® (automatic data direction control)

fibre-optic interface

Receive sensitivity	-20 dBm	Transmission mode: "Point-to-point"	Half-duplex, Full-duplex
Transmission mode: "Ring"	Half-duplex	Transmit power	> -5 dBm
Type of connection	ST connection, Multimode	Typical distances	5 km (50/125, 62.5/125, 100/140 µm multimode cable)
Wave length	850 nm		

EMC conformity and approvals

EMC standards	FCC Part 15 Class B, EN 61000-4-2 (ESD), Stage 3, EN 61000-4-3 (RS), Stage 2, EN 61000-4-4 (EFT), Stage 2, EN 61000-4-5 (Surge), Stage 3, EN 61000-4-6 (CS), EN 61000-4-8, Stage 1, cULus	Security	UL60950-1
---------------	---	----------	-----------

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	75 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	75 °C
Storage temperature, min.	-40 °C		

Guarantee

Time interval	5 years
---------------	---------

MTBF

MTBF	780,480 hrs	MTBF	Telcordia (Bellcore), GB
------	-------------	------	--------------------------

Industrial Ethernet
IE-MCT-1RS232/485-1ST**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Power supply**

Connection type	1 removable 3-pole terminal block	Current consumption	140 mA @ 12 V DC
Overload current protection	1.1 A	Reverse polarity protection	Available
Supply line protection	2 KV Burst (EFT), EN61000-4-4, 2 KV Surge, EN61000-4-5	Supply voltage, max	48 V DC
Supply voltage, min.	12 V DC	Voltage supply	24 V DC

Serial signals

RS-232	Tx, Rx, GND	RS-422	TxD+, TxD-, RxD+, RxD-, GND
RS-485 2-wire	Data+, Data-, GND	RS-485 4-wire	TxD+, TxD-, RxD+, RxD-, GND

Technical data

Housing main material	Aluminum	Protection degree	IP30
Type of mounting	Mounting plate, Wall mounting, when screwed in, TS 35, (with optional mounting kit IE-DINRAILMOUNT-KIT 1504430000)		

Classifications

ETIM 6.0	EC000310	eClass 6.2	19-17-01-14
eClass 9.0	19-17-01-14	eClass 9.1	19-17-01-14

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
Brochure/Catalogue	CAT 9 IETH 15/16 EN
User Documentation	Hardware Installation Guide