

Cable clamp for cable

fixing and tapping

O Quick-release lock to secure

the housing cover

24

Q

Even faster with DIGITUS[®] Professional patch panels

With our optimized DIGITUS[®] Professional patch panel, we offer you one thing above all – besides longstanding, established features such as integrated dust covers and shielded RJ45 sockets: **Quicker installation that gets by without complicated clamp mounting (cable fixation) and cable ties (tension relief).**

Thanks to manually adjustable **cable clamps**, you are spared all the labor-intensive and time-consuming steps. Furthermore, the costly screwing together of the casing cover is eliminated, since this can be fixed quickly and simply due to more effective **quick fasteners**.

www.digitus-professional.com

Our products for quick installation:

483 mm (19")-Patch Panel (LSA+) High Density, CAT 6,

DN-91624S-SL-EA, DN-91624S-SL-EA-G

Save a lot of space (only 0.5U) - With shutters for dust protection - Best performance and link quality for your network.





4PPoE

483 mm (19")-Patch Panel (LSA+) CAT 6, shielded DN-91624S-EA, DN-91624S-EA-B

Best performance and link quality for your network.



CAT

10 GBit

E

483 mm (19")-Patch Panel for Keystone Modules, **High Density, shielded**

DN-91422, DN-91424

The 24-port 0.5U Patch Panel offers a high density. As the

panel is only 0.5U in height, it allows to present 48 ports

on 1U (2 panels with 24 ports each) which can be installed.



Item Code	EAN	Connection type	Ports	Color	Unit	Shielding
DN-91624S-SL-EA-G	4016032444848	LSA(+)	24	Grey (RAL 7035)	0,5U	Yes
DN-91624S-SL-EA	4016032241614			Black (RAL 9005)		
DN-91624S-EA	4016032288428			Grey (RAL 7035)	10	
DN-91624S-EA-B	4016032440260			Black (RAL 9005)		
DN-91422	4016032343295	Keystone			0,5U	
DN-91424	4016032343318		48		10	

-Admana

AAAAAA AININA CONTRACTOR