

# WZ1001

## Clamp-on Current Transformer

 3-447-026-03  
 1/1.19

- Safe in compliance with IEC 61010
- Minimal transformation error
- Large jaw opening with 43 mm dia.
- Compact and handy
- Permanently connected safety cable



### Application

The clamp-on current transformer allows for the interruption-free measurement of alternating current by enclosing the electrical conductor or busbar.

The clamp-on current transformer is especially suited as accessory for measurements with the clipping multimeter METRALINE DM 61.

### Applicable Regulations and Standards

IEC 61 010-1 EN 61 010-1 VDE 0411-1	Safety requirements for electrical equipment for measurement, control and laboratory use
EN 61010-2-032	Particular requirements for hand-held and hand-manipulated current sensors for electrical test and measurement
EN 60529 VDE 0470-1	Test instruments and test procedures Protection provided by enclosures (IP code)
IEC 61 326/EN 61 326	Electromagnetic Compatibility (EMC)

### Characteristic Values

Nominal primary current	1 ... 1000 A AC
Output signal	1 mA AC / 1 A AC
Transmission ratio Input : output	1000 : 1
Accuracy / max.error	Class 1 (2,5 VA) (for current range from 1 A to 1000 A, 50 Hz)
Max. operating voltage	CAT III 600 V per IEC 61010
Frequency range	40 Hz ... 1 kHz
Jaw opening / conductor diameter	max. 43 mm
Dimensions (W x H x D)	92 x 39 x 220 mm
Weight	approx. 650 g
Cable length	1.5 m

### Standard Equipment

- 1 Clamp-on current transformer with connection cable and 4 mm safety plugs
- 1 Operating instructions

### Order Information

Description	Type	Article number
Clamp-on current transformer 1000:1	WZ1001	Z194A

# WZ1001

## Clamp-on Current Transformer

---

---

Edited in Germany • Subject to change without notice • A pdf version is available on the Internet

 **GOSSEN METRAWATT**

GMC-I Messtechnik GmbH  
Südwestpark 15  
90449 Nürnberg • Germany

Phone +49 911 8602-111  
Fax +49 911 8602-777  
E-Mail [info@gossenmetrawatt.com](mailto:info@gossenmetrawatt.com)  
[www.gossenmetrawatt.com](http://www.gossenmetrawatt.com)