

**SAK Series  
TW AKZ SW**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Product image****Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

| Type       | TW AKZ SW                                 |
|------------|-------------------------------------------|
| Order No.  | <a href="#">1417510000</a>                |
| Version    | SAK Series, Separation plate, 2 mm, black |
| GTIN (EAN) | 4050118220957                             |
| Qty.       | 50 pc(s).                                 |

**SAK Series**  
**TW AKZ SW**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Width      | 2 mm   | Width (inches)  | 0.079 inch |
| Height     | 37 mm  | Height (inches) | 1.457 inch |
| Depth      | 38 mm  | Depth (inches)  | 1.496 inch |
| Net weight | 3.02 g |                 |            |

**Temperatures**

|                                  |               |                                  |        |
|----------------------------------|---------------|----------------------------------|--------|
| Storage temperature, max.        | 40 °C         | Storage temperature, min.        | 10 °C  |
| Storage temperature              | 10 °C...40 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 120 °C        |                                  |        |

**Material data**

|                           |       |        |       |
|---------------------------|-------|--------|-------|
| Material                  | Wemid | Colour | black |
| UL 94 flammability rating | V-0   |        |       |

**System specifications**

|         |                    |
|---------|--------------------|
| Version | Intermediate plate |
|---------|--------------------|

**Additional technical data**

|         |    |
|---------|----|
| Snap-on | No |
|---------|----|

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000886    | ETIM 5.0   | EC002848    |
| ETIM 6.0   | EC000886    | eClass 6.2 | 27-14-92-14 |
| eClass 7.1 | 27-14-92-14 | eClass 8.1 | 27-14-11-33 |
| eClass 9.0 | 27-14-11-92 | eClass 9.1 | 27-14-11-33 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                  |                      |
|------------------|----------------------|
| Engineering Data | <a href="#">STEP</a> |
|------------------|----------------------|